

# UE410-2R03

Flexi Classic

**SAFETY CONTROLLERS**

**SICK**  
Sensor Intelligence.



Illustration may differ



### Ordering information

Type	Part no.
UE410-2R03	6026144

Other models and accessories → [www.sick.com/Flexi\\_Classic](http://www.sick.com/Flexi_Classic)

### Detailed technical data

#### Features

<b>Module</b>	Relay module
<b>Configuration method</b>	Hard wired

#### Safety-related parameters

<b>Safety integrity level</b>	SIL3 (IEC 61508) SILCL3 (EN 62061)
<b>Category</b>	Category 4 (EN ISO 13849)
<b>Performance level</b>	PL e (EN ISO 13849)

#### Interfaces

<b>Outputs</b>	2 enable current contacts
<b>Number of control inputs</b>	1 (B1)
<b>Number of enable current contacts</b>	2 (13/14, 23/24)
<b>Number of signalling current contacts</b>	1 (Y14)
<b>Number of contactor monitoring contacts</b>	1 (Y1/Y2)
<b>Connection type</b>	Plug-in screw-type terminals
<b>Display elements</b>	LEDs

#### Electrical data

<b>Protection class</b>	III (EN 61140)
<b>Voltage supply</b>	Via FLEXBUS+
<b>Power consumption</b>	≤ 1.6 W
<b>Internal power consumption</b>	≤ 1.6 W <sup>1)</sup>
<b>Overvoltage category</b>	II (EN 61131-2)
<b>Switching inputs</b>	
Terminals	B1

<sup>1)</sup> Via FLEXBUS+.

Input voltage	18 V DC ... 30 V DC
<b>Enable current contacts</b>	
Terminals	13/14, 23/24
Type of output	Potential-free NO contacts, positively guided
Switching voltage	5 V AC/DC ... 253 V AC/DC
Current-carrying capacity per OSSD	10 mA ... 6 A
<b>Signalling current contacts</b>	
Terminals	Y14
Type of output	NO contact, connected to internal 24 V DC, positively guided, current-limited
Output voltage	16 V DC ... 30 V DC
Output current	≤ 75 mA
<b>Contact monitoring contacts</b>	
Terminals	Y1/Y2
Type of output	Potential-free NC contacts, positively guided
Switching voltage	5 V AC/DC ... 253 V AC/DC
Current-carrying capacity per OSSD	10 mA ... 6 A

<sup>1)</sup> Via FLEXBUS+.

## Mechanical data

<b>Dimensions (W x H x D)</b>	22.5 mm x 96.5 mm x 120.8 mm
<b>Weight</b>	160 g (± 5 %)

## Ambient data

<b>Enclosure rating</b>	
Housing	IP40 (EN 60529)
Terminals	IP20 (EN 60529)
<b>Ambient operating temperature</b>	-25 °C ... +55 °C
<b>Storage temperature</b>	-25 °C ... +70 °C
<b>Air humidity</b>	15 % ... 95 %, Non-condensing
<b>Climate conditions according to</b>	EN 61131-2 (55 °C ambient operating temperature, 95% rel. humidity)
<b>Electromagnetic compatibility (EMC)</b>	Class A (EN 61000-6-2, EN 55011)
<b>Vibration resistance</b>	5 g RMS, 5 Hz ... 500 Hz (EN 60068-2-64)


## Classifications

<b>ECl@ss 5.0</b>	27242290
<b>ECl@ss 5.1.4</b>	27249090
<b>ECl@ss 6.0</b>	27249090
<b>ECl@ss 6.2</b>	27249090
<b>ECl@ss 7.0</b>	27249090
<b>ECl@ss 8.0</b>	27249090
<b>ECl@ss 8.1</b>	27249090
<b>ECl@ss 9.0</b>	27249090
<b>ETIM 5.0</b>	EC002632
<b>ETIM 6.0</b>	EC002632

UNSPSC 16.0901

32151705

Dimensional drawing (Dimensions in mm (inch))



## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)