

Base strip - DFK-IPCV 16/ 4-GF-10,16 - 1703234

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 76 A, Rated voltage (III/2): 1000 V, Number of positions: 4, Pitch: 10.16 mm, Color: green, Contact surface: Silver, Mounting: Soldering




The figure shows a 5-pos. version of the product

Why buy this product

- Panel thickness of 1 mm to 3 mm
- Inverted feed-through headers for implementing a touch-proof PCB output (in combination with IPC 16 ST)
- Tool-free snap-lock mechanism or conventional screw connection
- For soldering onto the PCB



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 046356 031745 |
| Weight per Piece (excluding packing) | 25.36 g |
| Custom tariff number | 85366990 |
| Country of origin | Poland |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|----------------|-----------|
| Length | 22 mm |
| Height | 34.55 mm |
| Pitch | 10.16 mm |
| Dimension a | 30.48 mm |
| Pin dimensions | 0,8 x 1,2 |
| Pin spacing | 10.16 mm |
| Hole diameter | 1.7 mm |

General

Base strip - DFK-IPCV 16/ 4-GF-10,16 - 1703234

Technical data

General

| | |
|---|--------------------|
| Range of articles | DFK-IPCV 16/...-GF |
| Insulating material group | I |
| Rated surge voltage (III/3) | 8 kV |
| Rated surge voltage (III/2) | 8 kV |
| Rated surge voltage (II/2) | 6 kV |
| Rated voltage (III/3) | 1000 V |
| Rated voltage (III/2) | 1000 V |
| Rated voltage (II/2) | 1000 V |
| Connection in acc. with standard | EN-VDE |
| Nominal current I_N | 76 A |
| Maximum load current | 76 A |
| Insulating material | PA |
| Inflammability class according to UL 94 | V0 |
| Color | green |
| Number of positions | 4 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27141190 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11 | 39121409 |
| UNSPSC 12.01 | 39121409 |
| UNSPSC 13.2 | 39121409 |

Approvals

Approvals

Base strip - DFK-IPCV 16/ 4-GF-10,16 - 1703234

Approvals

Approvals

UL Recognized / SEV / cUL Recognized / CCA / EAC / IEC60335 CB Scheme / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

| | | | |
|--------------------|-------|-------|-------|
| UL Recognized | | | |
| | B | C | D |
| Nominal current IN | 55 A | 55 A | 5 A |
| Nominal voltage UN | 300 V | 300 V | 600 V |

| | |
|--------------------|--------|
| SEV | |
| Nominal current IN | 76 A |
| Nominal voltage UN | 1000 V |

| | | | |
|--------------------|-------|-------|-------|
| cUL Recognized | | | |
| | B | C | D |
| Nominal current IN | 55 A | 55 A | 5 A |
| Nominal voltage UN | 300 V | 300 V | 600 V |

| | |
|--------------------|--------|
| CCA | |
| Nominal current IN | 76 A |
| Nominal voltage UN | 1000 V |

| |
|-----|
| EAC |
|-----|

Base strip - DFK-IPCV 16/ 4-GF-10,16 - 1703234

Approvals

| | |
|--------------------------------|--------|
| IECEE CB Scheme | |
| Nominal current I _N | 76 A |
| Nominal voltage U _N | 1000 V |

| | |
|------------------|--|
| cULus Recognized | |
|------------------|--|

Accessories

Accessories

Coding element

Coding profile - CP-PC RD - 1701967



Coding profile, for plugging into the coding ribs of the plug at a later date, insulating material, color: Red

Accessories - CS-IPC 16/ 6 - 1970016



Coding pin, serves to ensure correct polarization on the PCB during manual mounting

Mounting material

Accessories - DFK-PC 16-SS - 1705449



Screw set for DFK-PC 16... connectors

Screwdriver tools

Base strip - DFK-IPCV 16/ 4-GF-10,16 - 1703234

Accessories

Screwdriver - SZK PH1 VDE - 1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

Screwdriver - SZS 0,6X2,5 VDE - 1205040



Screwdriver, slot-headed, VDE insulated, size: 0.6 x 2.5 x 80 mm, 2-component grip, with non-slip grip

Additional products

Printed-circuit board connector - ISPC 16/ 4-STF-10,16 - 1748642



Plug component, Nominal current: 76 A, Rated voltage (III/2): 1000 V, Number of positions: 4, Pitch: 10.16 mm, Connection method: Spring-cage connection, Color: green, Contact surface: Silver

Printed-circuit board connector - IPC 16/ 4-STF-10,16 - 1969470



Plug component, Nominal current: 76 A, Rated voltage (III/2): 1000 V, Number of positions: 4, Pitch: 10.16 mm, Connection method: Screw connection, Color: green, Contact surface: Silver

Printed-circuit board connector - IPC 16/ 4-STF-SH-10,16 - 1970346




Plug component, Nominal current: 76 A, Rated voltage (III/2): 1000 V, Number of positions: 4, Pitch: 10.16 mm, Connection method: Screw connection, Color: green, Contact surface: Silver


Drawings

Base strip - DFK-IPCV 16/ 4-GF-10,16 - 1703234

Drilling diagram




Diagram




The illustration shows the derating curve for DFK-IPC 16/..-G-10,16 inverted plugs in combination with the inverted header IPC 16/..-ST-10,16.

Dimensioned drawing



Sheet metal cutout for snap-on.

Dimensioned drawing



Sheet metal cutout for screw connection.

Dimensioned drawing

