

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

N

REVISED PER ECO-12-007492

03AUG12

KH

SM

1

MATERIAL: CONNECTOR - NYLON UL94V-2.
CONTACTS - 0.30[.012] THICK COPPER ALLOY
BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
FOR 640440-2 THRU 2-640440-8.
MATTE WHISKER MITIGATED TIN .00203[.000080] MIN THICKNESS OVER
NICKEL UNDERPLATE FOR 3-640440-2 THRU 5-640440-8.

2

CONTACTS ACCEPT 22 AWG WIRE WITH 1.52[.060] MAX
INSULATION DIAMETER.

3

CONTACTS MUST ACCEPT 0.64±0.03[.025±.001]
POST AND REMAIN LOCKED IN POSITION.

4

IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY
NOT APPEAR ON ALL ASSEMBLIES.

5

DIMENSIONS IN BRACKETS ARE IN INCHES.

6

HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP.

7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8

RED COLOR STRIPE ON HOUSING (NOT SHOWN) MAY RUN DOWN BETWEEN RIBS.

YES

71.12[2.800]

28

5-640440-8

YES

68.58[2.700]

27

5-640440-7

YES

66.04[2.600]

26

5-640440-6

YES

63.50[2.500]

25

5-640440-5

YES

60.96[2.400]

24

5-640440-4

YES

58.42[2.300]

23

5-640440-3

YES

55.88[2.200]

22

5-640440-2

YES

53.34[2.100]

21

5-640440-1

YES

50.80[2.000]

20

5-640440-0

YES

48.26[1.900]

19

4-640440-9

YES

45.72[1.800]

18

4-640440-8

YES

43.18[1.700]

17

4-640440-7

YES

40.64[1.600]

16

4-640440-6

YES

38.10[1.500]

15

4-640440-5

YES

35.56[1.400]

14

4-640440-4

YES

33.02[1.300]

13

4-640440-3

YES

30.48[1.200]

12

4-640440-2

YES

27.94[1.100]

11

4-640440-1

YES

25.40[1.000]

10

4-640440-0

YES

22.86[.900]

9

3-640440-9

YES

20.32[.800]

8

3-640440-8

YES

17.78[.700]

7

3-640440-7

YES

15.24[.600]

6

3-640440-6

YES

12.70[.500]

5

3-640440-5

YES

10.16[.400]

4

3-640440-4

YES

7.62[.300]

3

3-640440-3

YES

5.08[.200]

2

3-640440-2

NO

71.12[2.800]

28

2-640440-8

SUP BY 5-640440-8

7

NO

68.58[2.700]

27

2-640440-7

SUP BY 5-640440-7

7

NO

66.04[2.600]

26

2-640440-6

NO

63.50[2.500]

25

2-640440-5

SUP BY 5-640440-5

7

NO

60.96[2.400]

24

2-640440-4

NO

58.42[2.300]

23

2-640440-3

OBSOLETE

NO

55.88[2.200]

22

2-640440-2

SUP BY 5-640440-2

7

NO

53.34[2.100]

21

2-640440-1

NO

50.80[2.000]

20

2-640440-0

NO

48.26[1.900]

19

1-640440-9

NO

45.72[1.800]

18

1-640440-8

NO

43.18[1.700]

17

1-640440-7

NO

40.64[1.600]

16

1-640440-6

NO

38.10[1.500]

15

1-640440-5

NO

35.56[1.400]

14

1-640440-4

NO

33.02[1.300]

13

1-640440-3

NO

30.48[1.200]

12

1-640440-2

NO

27.94[1.100]

11

1-640440-1

NO

25.40[1.000]

10

1-640440-0

NO

22.86[.900]

9

640440-9

NO

20.32[.800]

8

640440-8

NO

17.78[.700]

7

640440-7

NO

15.24[.600]

6

640440-6

NO

12.70[.500]

5

640440-5

NO

10.16[.400]

4

640440-4

NO

7.62[.300]

3

640440-3

NO

5.08[.200]

2

640440-2

LEADFREE

DIM A

NO. OF CIRCUITS

PART NO.

6.99
[.275]

6.22
[.245]

13.21
[.520]

6.99
[.275]

1.91
[.075]

4.67±0.08
[.184±.003]

3.66±0.08
[.144±.003]

1.42±0.10
[.056±.004]

6.99
[.275]

AMP
1 2 3

1

2

3

4

TE

TE Connectivity

MTA 100 CONNECTOR ASSEMBLY,
22 AWG, STANDARD

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=640440

-

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 of 1

REV N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ± 0.13 [.005]

4 PLC ±

ANGLES ±

FINISH 1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

N

REVISED PER ECO-12-007492

03AUG12

KH

SM

1

MATERIAL: CONNECTOR - NYLON UL94V-2.
CONTACTS - 0.30[.012] THICK COPPER ALLOY
BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
FOR 640440-2 THRU 2-640440-8.
MATTE WHISKER MITIGATED TIN .00203[.000080] MIN THICKNESS OVER
NICKEL UNDERPLATE FOR 3-640440-2 THRU 5-640440-8.

2

CONTACTS ACCEPT 22 AWG WIRE WITH 1.52[.060] MAX
INSULATION DIAMETER.

3

CONTACTS MUST ACCEPT 0.64±0.03[.025±.001]
POST AND REMAIN LOCKED IN POSITION.

4

IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY
NOT APPEAR ON ALL ASSEMBLIES.

5

DIMENSIONS IN BRACKETS ARE IN INCHES.

6

HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP.

7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8

RED COLOR STRIPE ON HOUSING (NOT SHOWN) MAY RUN DOWN BETWEEN RIBS.

6.99
[.275]

6.22
[.245]

13.21
[.520]

6.99
[.275]

1.91
[.075]

4.67±0.08
[.184±.003]

3.66±0.08
[.144±.003]

1.42±0.10
[.056±.004]

6.99
[.275]

AMP
1 2 3

1

2

3

4

TE

TE Connectivity

MTA 100 CONNECTOR ASSEMBLY,
22 AWG, STANDARD

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=640440

-

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 of 1

REV N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ± 0.13 [.005]

4 PLC ±

ANGLES ±

FINISH 1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

N

REVISED PER ECO-12-007492

03AUG12

KH

SM

1471-9 (3/11)