



FEMALE END VIEW



- 1 = GRN
- 2 = RED/BLK
- 3 = RED/WHIT



SPECIFICATIONS	
CONTACT CARRIER MATERIAL	NYLON
MOLDED HEAD MATERIAL/COLOR	THERMOPLASTIC PUR/YELLOW
CONTACT MATERIAL/PLATING	GOLD-PLATED BRASS
COUPLING NUT	NICKEL-PLATED BRASS
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
OUTER JACKET MATERIAL/COLOR	PVC/YELLOW
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	3x22 AWG
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67



CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
2. STRIP AND TIN LENGTHS ARE FOR REFERENCE ONLY; SOME LENGTHS MAY NOT BE STRIPPED AND TINNED.

A	DRAWING RELEASE	RDS	01/28/02	T5138
REV	DESCRIPTION	BY	DATE	ECO NO.

RELATED DOCUMENTS	1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DOCUMENT IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	DATE 02/16/01	DESCRIPTION
MATERIAL	SEE SPECIFICATIONS	TOLERANCES UNLESS OTHERWISE SPECIFIED	DRFT JBU	SCALE 1=1.0	KB 3T-*
FINISH	SEE SPECIFICATIONS	.X ±0.02 .XX ±0.01 XXX ±0.005 ANGLES ±1°	UNIT OF MEASUREMENT INCH [MILLIMETER]	DO NOT SCALE THIS DRAWING	IDENTIFICATION NO.
SEE SPECIFICATIONS		ALL MILLIMETER DIMENSIONS ARE REFERENCE ONLY			REV
					A

SOURCE DRAWING - FOR REFERENCE ONLY

TURCK inc
High Technology Sensors and Automation Controls

3000 CAMPUS DRIVE
MINNEAPOLIS, MN 55441
1-800-544-7769
(763) 553-7300
(763) 553-0708 fax
turck.com