

Classic ECO Candle

Classic ECO Candle 42W E14 230V Sleeve

0023771



Range features

- 1:1 replacement of Incandescent Candle lamp
- More efficient - more savings
- Up to two times more average life compared to incandescent lamps = 2000 hours
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Sparkling light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- 100% dimmable



PRODUCT OVERVIEW

| | |
|----------------------------|---------------|
| Ordering number | 0023771 |
| Light colour | 828 Homelight |
| Technology | Halogen |
| Energy class | D |
| Average life (Rated) (h) | 2000 |
| Lamp finish | Clear |
| Lamp shape | Candle |
| Dimmable | Yes |
| Cap/Base | E14 |
| Type | Candle ECO |
| EAN code | 5410288237718 |
| CRI (Ra) | 100 |
| Beam angle(°) | na |
| Colour temperature (K) | 2800 |
| Luminous flux (Rated) (lm) | 625 |
| Watt (Nominal) (W) | 42 |
| Equivalent watt (W) | 55 |
| Voltage (V) | 230 |

Classic ECO Candle

Classic ECO Candle 42W E14 230V Sleeve

0023771

DATA TABLE

General data

| | |
|--|---|
| Ordering number | 0023771 |
| Technology | Halogen |
| Average life (Rated) (h) | 2000 |
| Average life (Nominal) (h) | 2000 |
| Energy saving lamp | No |
| Energy class | D |
| Lamp finish | Clear |
| Lamp shape | Candle |
| Dimmable | Yes |
| Cap/Base | E14 |
| Type | Candle ECO |
| EAN code | 5410288237718 |
| Long description | 1:1 replacement of Incandescent Candle lamp. More efficient - more savings. Up to two times more average life compared to incandescent lamps = 2000 hours. Excellent colour rendering (CRI = 100). Instant illumination. Sparkling light output. Less heat generation than incandescent lamp. Less CO2 emissions. Identical shape as standard incandescent lamp. Commercial and domestic application. 100% dimmable |
| Product name | Classic ECO Candle 42W E14 230V Sleeve |
| Lamp mercury content (mg) | 0 |
| Starting time (max) (s) | 0.01 |
| Warm-up time to 60% of full light (max) (s) | Instant full light |
| Control gear required | No |
| Fixture rating | Open |
| IEC Reference | IEC 60357 |
| IEC Reference 2 | IEC 60432-2 |
| Intended purpose | General lighting |
| No. of switching cycles before premature failure (min) | > 8000 |
| Special purpose lamp | No |
| Transformer required | No |
| Sales pack quantity | 10 |
| Optimal operating condition (°C) | 25 |

Classic ECO Candle

Classic ECO Candle 42W E14 230V Sleeve

0023771

Optical data

| | |
|--|---------------|
| Light colour | 828 Homelight |
| CRI (Ra) | 100 |
| Suitable for accent lighting | No |
| Beam angle(°) | na |
| Colour temperature (K) | 2800 |
| Luminous flux (Rated) (lm) | 625 |
| Lumen maintenance at end of nominal life (%) | 80 |
| Luminous flux (Nominal) (lm) | 625 |

Electrical data

| | |
|---------------------------------|-----|
| kWh per 1000 hours burning time | 42 |
| Watt (Rated) (W) | 42 |
| Watt (Nominal) (W) | 42 |
| Equivalent watt (W) | 55 |
| Voltage (V) | 230 |
| Lamp power factor | 1 |

Physical data


| | |
|------------------------------|------|
| Lamp Length (mm) - C/L | 100 |
| Lamp Diameter (mm) - D | 36 |
| Packaging outer width (cm) | 20 |
| Packaging outer length (cm) | 37.5 |
| Packaging outer height (cm) | 22.5 |
| Packaging single width (cm) | 3.55 |
| Packaging single length (cm) | 3.55 |
| Packaging single height (cm) | 10.1 |

Classic ECO Candle

Classic ECO Candle 42W E14 230V Sleeve

0023771

TECHNICAL DRAWINGS



ENERGY LABEL

