


Tapered roller bearings, single row



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass kg	Designation
d	D	T	dynamic	static		Reference speed	Limiting speed		
mm			kN	C_0	kN	r/min			-
40	80	19,75	61,6	68	7,65	6300	8500	0,42	30208 J2/Q



Calculation factors

e 0,37
 Y 1,6
 Y_0 0,9