

Contact insert module - HC-M-EMV-MOD-BU - 1678570


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON series M EMC contact insert module, for using two HC-M-EMV-BU/3-9.5 EMC connectors (socket version, each 4-pos.)



Key commercial data

Packing unit	2 pc
Minimum order quantity	2 pc
GTIN	 4 017918 167707
Weight per Piece (excluding packing)	15.13 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Electrical characteristics

Note	For housing HC-B6 to B48, for housing HC-ADVANCE-B6 to B24, hinged retaining frame HC-M-MHR... necessary
------	--

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical characteristics

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

General

Series	HC-M-EMV
Number of module slots	2
Inflammability class according to UL 94	V0
Assembly instructions	Housing height ≥ 72 mm. Plug-in connections may only be operated only when there is no load/voltage.
Connection	Plastic module for the HC-M-EMV-BU/3-9.5 EMC connector

Material data

Contact insert module - HC-M-EMV-MOD-BU - 1678570

Technical data

Material data

Contact carrier material	PC
--------------------------	----

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

Contact insert module - HC-M-EMV-MOD-BU - 1678570

Approvals

UL Recognized


cUL Recognized

GOST

cULus Recognized

Drawings

Dimensioned drawing



Female insert