

High Precision Ambient Light Photodiode

Version 1.4

SFH 2270R



Features:

- Nearly perfect match with Human Eye Sensitivity (V_λ)
- Black coloured TOPLED®-package
- Low leakage current

Applications

- Ambient light sensor

Ordering Information

Type:	Photocurrent I_p [μA] $\lambda = 560 \text{ nm}$, $E_e = 0.01 \text{ mW/cm}^2$, $V_R = 1 \text{ V}$	Ordering Code
SFH 2270R	0.0056 (≥ 0.0044)	Q65110A9911

Note: corresponds to an illuminance of app. 55 lx

Maximum Ratings ($T_A = 25\text{ °C}$)


Parameter	Symbol	Values	Unit
Operating and storage temperature range	$T_{op}; T_{stg}$	-40 ... 100	°C
Reverse voltage	V_R	2	V
ESD withstand voltage (acc. to ANSI/ ESDA/ JEDEC JS-001 - HBM)	V_{ESD}	2000	V

Characteristics ($T_A = 25\text{ °C}$)

Parameter	Symbol	Values	Unit
Recommended operating range for illuminance (typ)	E_V	(typ) 5 ... 100000	lx
Photocurrent ($V_R = 1\text{ V}$, $E_V = 1000\text{ lx}$, standard light A) (typ (min))	I_P	0.1	μA
Photocurrent ($V_R = 1\text{ V}$, $E_e = 10\mu\text{W}/\text{cm}^2$, $\lambda = 560\text{ nm}$ (corresponds to an illuminance of app. 55 lx)) (typ (min))	I_P	0.0056 (≥ 0.0044)	μA
Wavelength of max. sensitivity (typ)	$\lambda_{S\text{ max}}$	560	nm
Spectral range of sensitivity (typ)	$\lambda_{10\%}$	(typ) 480 ... 650	nm
Radiant sensitive area (typ)	A	0.16	mm^2
Dimensions of radiant sensitive area (typ)	L x W	0.4 x 0.4	mm x mm
Half angle (typ)	φ	± 60	°
Dark current ($V_R = 1\text{ V}$) (typ (max))	I_R	0.005 (≤ 0.15)	nA
Rise and fall time ($R_L = 50\text{ k}\Omega$; $V_R = 1\text{ V}$, $I_p = 4\mu\text{A}$, white LED) (typ)	t_r, t_f	6	μs
Capacitance ($V_R = 0\text{ V}$, $f = 1\text{ MHz}$, $E = 0$) (typ)	C_0	42	pF
Temperature coefficient of I_{SC} (typ)	TC_I	0.17	% / K


Relative Spectral Sensitivity ^{1) page 11}

$S_{rel} = f(\lambda)$




Dark Current ^{1) page 11}

$I_R = f(V_R), E = 0$




Capacitance ^{1) page 11}

$C = f(V_R), f = 1 \text{ MHz}, E = 0$




Directional Characteristics ^{1) page 11}

$S_{rel} = f(\phi)$



Package Outline




Dimensions in mm (inch).

Package


TOPLED Reverse Gullwing

Approximate Weight:
35 mg

Recommended Solder Pad



Component Location on Pad




E062.3010.05-02

Dimensions in mm.

Reflow Soldering Profile

Product complies to MSL Level 3 acc. to JEDEC J-STD-020D.01




OHA04612

Profile Feature Profil-Charakteristik	Symbol Symbol	Pb-Free (SnAgCu) Assembly			Unit Einheit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*) 25 °C to 150 °C			2	3	K/s
Time t_S T_{Smin} to T_{Smax}	t_S	60	100	120	s
Ramp-up rate to peak*) T_{Smax} to T_P			2	3	K/s
Liquidus temperature	T_L	217			°C
Time above liquidus temperature	t_L		80	100	s
Peak temperature	T_P		245	260	°C
Time within 5 °C of the specified peak temperature $T_P - 5$ K	t_P	10	20	30	s
Ramp-down rate* T_P to 100 °C			3	6	K/s
Time 25 °C to T_P				480	s

All temperatures refer to the center of the package, measured on the top of the component

* slope calculation DT/Dt : Dt max. 5 s; fulfillment for the whole T-range

Taping




OHAY2272

Dimensions are specified as follows: mm (inch).

Tape and Reel

12 mm tape with 2000 pcs. on \varnothing 180 mm reel, 8000 pcs. on \varnothing 330 mm reel



Leader: min. 400 mm *

Trailer: min. 160 mm *

*) Dimensions acc. to IEC 60286-3; EIA 481-D

OHAY0324

Tape dimensions [mm]


W	P ₀	P ₁	P ₂	D ₀	E	F
12 + 0.3 / - 0.1	4 ± 0.1	4 ± 0.1 or 8 ± 0.1	2 ± 0.05	1.5 ± 0.1	1.75 ± 0.1	5.5 ± 0.05

Reel dimensions [mm]


A	W	N _{min}	W ₁	W _{2max}
180	12	60	12.4 + 2	18.4

A	W	N _{min}	W ₁	W _{2max}
330	12	60	12.4 + 2	18.4

Barcode-Product-Label (BPL)



Dry Packing Process and Materials




Note:

Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card. Regarding dry pack you will find further information in the internet. Here you will also find the normative

references like JEDEC.

Transportation Packing and Materials



Dimensions of transportation box in mm

Width	Length	Height
195 ± 5	195 ± 5	30 ± 5
349 ± 5	349 ± 5	33 ± 5

Disclaimer

Language english will prevail in case of any discrepancies or deviations between the two language wordings.

Attention please!

The information describes the type of component and shall not be considered as assured characteristics.

Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version in the Internet.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office.

By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Components used in life-support devices or systems must be expressly authorized for such purpose!

Critical components* may only be used in life-support devices** or systems with the express written approval of OSRAM OS.

*) A critical component is a component used in a life-support device or system whose failure can reasonably be expected to cause the failure of that life-support device or system, or to affect its safety or the effectiveness of that device or system.

**) Life support devices or systems are intended (a) to be implanted in the human body, or (b) to support and/or maintain and sustain human life. If they fail, it is reasonable to assume that the health and the life of the user may be endangered.

Glossary

- ¹⁾ **Typical Values:** Due to the special conditions of the manufacturing processes of LED, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.

Published by OSRAM Opto Semiconductors GmbH
Leibnizstraße 4, D-93055 Regensburg
www.osram-os.com © All Rights Reserved.

EU RoHS and China RoHS compliant product



此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，不含有毒有害物质或元素。