

DOL-2312-G03MMA3

SICK
Sensor Intelligence.



Ordering information

Type	Part no.
DOL-2312-G03MMA3	2029213

Other models and accessories → www.sick.com/

Detailed technical data


Technical specifications

Accessory group	Plug connectors and cables				
Accessory family	Connecting cables				
Connection type head A	Female connector, M23, 12-pin, straight				
Connection type head B	Flying leads				
Locking nut material	Zinc die-cast, nickel-plated				
Cable	3 m, 12-wire, PUR				
Jacket material	PUR				
Jacket color	Black				
Cable diameter	7.8 mm				
Conductor cross-section	4 x 2 x 0.25 mm ² + 2 x 0,5 mm ² + 2 x 0.14 mm ²				
Shielding	Shielded				
Bending radius	<table border="0"> <tr> <td style="padding-right: 20px;">Stationary position</td> <td>> 5 x cable diameter</td> </tr> <tr> <td>Drag chain operation</td> <td>> 7.5 x cable diameter</td> </tr> </table>	Stationary position	> 5 x cable diameter	Drag chain operation	> 7.5 x cable diameter
Stationary position	> 5 x cable diameter				
Drag chain operation	> 7.5 x cable diameter				
Reference voltage	≤ 160 V				
Current loading	7 A				
Signal type	Incremental				
Enclosure rating	IP66/ IP67				
Description	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm ² + 2 x 0.5 mm ² + 1 x 0.14 mm ² , Ø 7.8 mm)				

Classifications

ECl@ss 5.0	19030312
ECl@ss 5.1.4	19030312
ECl@ss 6.0	27060304
ECl@ss 6.2	27060304
ECl@ss 7.0	27060304
ECl@ss 8.0	27060304
ECl@ss 8.1	27060304
ECl@ss 9.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
UNSPSC 16.0901	26121604

Dimensional drawing (Dimensions in mm (inch))



- ① Black
- ② Gray
- ③ Purple
- ④ Yellow
- ⑤ White
- ⑥ Brown
- ⑧ Pink
- ⑨ Screen
- ⑩ Blue
- ⑪ Green
- ⑫ Red

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com