

# Neodymium Ring Magnet datasheet

## Countersunk hole

- Neodymium iron boron 'rare earth' material
- Strongest magnet material available
- 80°C max. operating temp.
- High resistance to de-magnetisation
- Anisotropic
- N35 grade



### Product Information

| Product No. | Diameter | Hole          | Hole            | Unit/Pack |
|-------------|----------|---------------|-----------------|-----------|
|             |          | Outer Diamner | Inner diamerter |           |
| <i>mm</i>   |          |               |                 |           |
| N832RS      | 15.4     | 3.3           | 3.25            | 5         |
| N833RS      | 19       | 4.5           | 7.6             | 5         |
| N834RS      | 17.5     | 4.5           | 4               | 5         |