



RoHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
 *4	C	ECR #070330-3 ADD ROHS, EDIT CABLE SPEC,PACKING,CONN	04/03/07'
 *2	D	ECR #090224-2 EDIT PACKING,ADD BAR CODE NO.	02/24/09'



NOTE:

- CABLE:
UL2725 80°C 30V [26AWG(1/0.404 T.C)*2F + AL/MY+DRAIN WIRE(1/0.32 T.C)*2]
 INS: FOAM-PE OD: $\phi 1.1 \pm 0.05$ mm
PVC JACKET OD: $\phi (2.2 \pm 0.1) * (7.8 \pm 0.2)$ mm COLOR: RED (PANTONE 200C)
IMPEDANCE: 100 ± 5 OHM
- CONNECTOR: 2-1 MATERIAL:
 HOUSING: HIGH TEMPERATURE POLYESTER & GLASS FIBER UL 94V-0
TERMINAL: COPPER ALLOY, CRIMP TYPE
2-1 PLATING: CONTACT AREA: G/F
- HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01)
- CABLE ASS'Y ELECTRICAL TEST: 4-1 100% OPEN SHORT & MIS WIRE TEST
4-2 CONTACT RESISTANCE 2 OHM MAX
4-3 INSULATION RESISTANCE 20M OHM MIN
- PACKING: EACH PC / POLYBAG + HEADER CARD + P/N LABEL
   100 PCS / INNER CARTON, 2 INNER CARTON / MASTER CARTON



Tolerance Inch M/M		
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Draw
FANNIE 02/24/09'

Check
Engr

Rotronic Co., Ltd.

Title
SERIAL ATA SIGNAL CABLE

Customer P/N

App'd Customer T-RAG

Scale NONE Units m/m Third Angle Projection 

Dwg No. 140-1099 REV: E Sheet 1/1

DWG	P/N	L (mm)	T (mm)	INNER CTN(mm)	MASTER CTN(mm)	BAR CODE NO.
140-1099-2	11.03.1561	1000	20	360*310*150	380*330*340	7611990160518
140-1099-1	11.03.1556	500	20	360*310*100	380*330*240	7611990160501