

## SAPPHIRE® Extreme 2

### High load, high temperature MoS<sub>2</sub> bearing grease

#### Product Overview

ROCOL® SAPPHIRE Extreme 2 is a heavy duty, high temperature bearing grease fortified with molybdenum disulphide. It has been designed for the effective lubrication and protection of ball, roller and plain bearings used in extreme environments.

SAPPHIRE Extreme 2 combines the resilience of a clay thickener with the addition of molybdenum disulphide ensuring that a lubricating film exists under the most extreme loadings where the grease film can be squeezed out.

#### Features and Benefits

- Excellent high temperature resistance – operating from -10°C to +235°C.
- Non-melting, organically modified clay (Bentone) thickened, grease, fortified with molybdenum disulphide, for excellent high temperature and water resistance.
- Molybdenum disulphide (MoS<sub>2</sub>) has an affinity to metal surfaces leaving a tenacious high load carrying film with a low coefficient of friction. This film provides an extremely durable layer, reducing frictional heat and wear and extending component life and lubrication intervals.
- Ideal for highly loaded applications, where shock loads and vibration can occur.
- Highly resistant to oxidation, providing extended lubrication intervals over conventional lubricants.
- Excellent corrosion resistance to protect in humid, damp and even wet conditions.
- Highly tenacious lubricants, with outstanding film strength, ensure the lubricants remain in place even in severe operating conditions.
- SAPPHIRE Extreme 2 maintains its integrity in extreme conditions and continues to protect over extended lubrication intervals, reducing equipment failure, downtime and lubricant usage.

#### Directions for Storage and Use

- SAPPHIRE Extreme 2 can be applied manually, by grease gun, keg pump or by other methods suitable for dispensing NLGI No. 2 greases with solid additives.
- SAPPHIRE Extreme 2 is compatible with other clay thickened greases. However, for best results the previous lubricant should be removed prior to application.
- Avoid mixing SAPPHIRE Extreme 2 with soap thickened greases.
- The storage temperature should be controlled between +1°C and +40°C.
- Shelf life is 3 years from date of manufacture.

#### Typical Applications

SAPPHIRE Extreme 2 is particularly suitable for high temperature bearings operating in extreme conditions such as shock loads, vibration and wet environments.

It is designed for all types of ball, roller and plain bearings typically found in industries such as steelworks, quarries, mining, marine, docks, agriculture, construction, brick and tile works and other industries particularly where ovens or similar heavy duty, high temperature applications are found.

SAPPHIRE Extreme 2 excels in applications such as ovens, furnaces, kiln cars, crushers, screens, presses, loaders, scrapers, wagons and similar applications where bearings, pins, bushes, slides etc. are subjected to extreme conditions.

#### Pack Sizes

| Pack Size      | Part Code |
|----------------|-----------|
| 400g cartridge | 12211     |
| 5kg            | 12216     |
| 18kg           | 12214     |
| 50kg           | 12218     |

## SAPPHIRE® Extreme 2

High load, high temperature MoS<sub>2</sub> bearing grease

| Property                           | Test Method         | Result                     |
|------------------------------------|---------------------|----------------------------|
| Appearance                         | Visual              | Smooth blue / black grease |
| NLGI No.                           | IP 50 – ASTM D217   | 2                          |
| Base Type                          | N/A                 | Semi-synthetic             |
| Base Fluid Viscosity at 40°C       | IP 71               | 200cSt                     |
| Base Fluid Viscosity at 100°C      | IP 71               | 20cSt                      |
| Thickener                          | N/A                 | Organically modified clay  |
| Solids                             | N/A                 | Molybdenum disulphide      |
| Temperature Range - Upper Limit    | N/A                 | -10°C to + 235°C           |
| Temperature Range - Short Periods  | N/A                 | Up to +250°C               |
| 4-Ball Weld Load                   | IP 239 – ASTM D2596 | 280kg                      |
| 4-Ball Mean Hertz Load             | IP 239 – ASTM D2596 | 50kg                       |
| Oil Separation<br>24 hrs at +100°C | IP 121              | 5% maximum                 |
| Water Washout Test                 | IP 215 – ASTM D1264 | 0%                         |
| Emcor Corrosion Test               | IP 220              | 0:0                        |
| Corrosion Test:                    |                     |                            |
| 24 hrs at +100°C Copper            | IP 112 – ASTM D130  | 1a                         |
| Corrosion Test - Mild Steel        | 24 hrs at 100°C     | No stain                   |
| Corrosion Test - Aluminium         | 24 hrs at 100°C     | No stain                   |

Values quoted above are typical and do not constitute a specification.

### Safety Data Sheets

Safety data sheets are available for download from our website [www.rocol.com](http://www.rocol.com) or may be obtained from your usual ROCOL contact.

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

Issue: 2 Date: 05-12

T +44 (0) 113 232 2600

F +44 (0) 113 232 2740

E [customer-service@rocol.com](mailto:customer-service@rocol.com)

[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67

Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001  
Certificate No. FM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAS 18001  
Certificate No. OHS 78173



INVESTORS  
IN PEOPLE