

Double-deck terminal blocks

Compression clamp


DIN 1 - 3

End stop	th. 9,1 mm	BAMH	0114 836.00
<i>Other end stops : See Accessories section</i>			
Rail	35 x 7,5 x 1	PR30 prepunched	0173 220.05
Rail	35 x 15 x 2,3	PR4	0168 500.12
Rail	35 x 15 x 1,5	PR5 prepunched	0101 598.26
Rail	32 x 15 x 1,5	PR1Z2	0163 050.04
<i>Other rails : See Accessories section</i>			
<i>Other accessories : See Accessories section</i>			

Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.


Accessories



1 End section	grey blue beige		
2 Circuit separator	grey		
3 Test socket			
4 Test device			
5 Test plug			
6 Assembled jumper bar (without IP 20 protection)	24 A 24 A 24 A		
7 Assembled jumper bar (with IP 20 protection)	24 A 24 A 24 A		
8 Jumper bar not assembled	24 A		
Screw + washer + post			
9 Comb type jumper bar	30 A 30 A		
Insulating tip			
10 Vertical jumper bar			
11 Shield connector			
R See section on markers marking method			

MA 2,5/5.D2...

Spacing 5 mm +0,08 (.200")



Standard 5 mm block

Color	Type	Part numbers
Grey	MA 2,5/5.D2	0115 490.13
Blue	MA 2,5/5.D2.N	0125 490.15
Beige V0	MA 2,5/5.D2.V0	0195 490.14


Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
Compression Solid wire	0,2-4 mm ²		24-12 AWG	24-12 AWG
clamp Stranded wire	0,22-2,5 mm ²		24-12 AWG	24-12 AWG

Voltage			
Rated	630 V	300 V	300 V
Pulse	8 kV		
Pollution degree	3		
Current			
Rated	24 A	20 A	25 A
Wire size			
Rated / Gauge	2,5 mm ² / A3	12 AWG	12 AWG
Wire stripping length	Recomm. Screwdriver	Recomm. torque	Protection
9 mm	3,5 mm	0,4-0,6 Nm	IP20
.354"	.138"	3.5-5.3 lb.in	NEMA 1

MA 2,5/5.D2.1...

Spacing 5 mm +0,08 (.200")



MA 2,5/5.D2 with partition

Color	Type	Part numbers
Grey	MA 2,5/5.D2.1	0115 491.00
Blue	MA 2,5/5.D2.1N	0125 491.02

Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
Compression Solid wire	0,2-4 mm ²		24-12 AWG	24-12 AWG
clamp Stranded wire	0,22-2,5 mm ²		24-12 AWG	24-12 AWG

Voltage			
Rated	630 V	300 V	300 V
Pulse	8 kV		
Pollution degree	3		
Current			
Rated	24 A	20 A	25 A
Wire size			
Rated / Gauge	2,5 mm ² / A3	12 AWG	12 AWG
Wire stripping length	Recomm. Screwdriver	Recomm. torque	Protection
9 mm	3,5 mm	0,4-0,6 Nm	IP20
.354"	.138"	3.5-5.3 lb.in	NEMA 1

Type	Part numbers
FEM6D th. 1,0 mm	0118 499.23
FEM6D th. 1,0 mm	0128 499.25
FEM6D V0 V0 th. 1,0 mm	0198 499.24
SCMA5D th. 1,0 mm	0116 720.21
AL2 (1) DIA. 2,0 mm	0164 950.00
DCV green	0173 058.02
FC2 (3) DIA. 2,0 mm	0007 865.26
BJM5D (1) 2 poles	0176 226.22
BJM5D (1) 3 poles	0176 227.23
BJM5D (1) 4 poles	0176 228.04
BJM5D (1) 5 poles	0176 229.05
BJM5D (1) 10 poles	0176 230.02
BJMI5D (1) 2 poles	0176 736.21
BJMI5D (1) 3 poles	0176 737.22
BJMI5D (1) 4 poles	0176 738.03
BJMI5D (1) 5 poles	0176 739.04
BJMI5D (1) 10 poles	0176 740.11
BJS5D (1) 20 poles	0177 651.05
EV5D	0176 260.10
PC5 2 poles	0113 542.10
PC5 10 poles	0113 544.12
EIP	0113 550.24
ITV5	0176 259.13
CBM5D th. 0,5 mm	0173 530.24

Type	Part numbers
FEM6D th. 1,0 mm	0118 499.23
FEM6D th. 1,0 mm	0128 499.25
FEM6D V0 V0 th. 1,0 mm	0198 499.24
AL2 DIA. 2,0 mm	0164 950.00
DCV green	0173 058.02
FC2 (3) DIA. 2,0 mm	0007 865.26
BJM5D (2) 2 poles	0176 226.22
BJM5D (2) 3 poles	0176 227.23
BJM5D (2) 4 poles	0176 228.04
BJM5D (2) 5 poles	0176 229.05
BJM5D (2) 10 poles	0176 230.02
BJMI5D (2) 2 poles	0176 736.21
BJMI5D (2) 3 poles	0176 737.22
BJMI5D (2) 4 poles	0176 738.03
BJMI5D (2) 5 poles	0176 739.04
BJMI5D (2) 10 poles	0176 740.11
BJS5D (2) 20 poles	0177 651.05
EV5D	0176 260.10
PC5 2 poles	0113 542.10
PC5 10 poles	0113 544.12
EIP	0113 550.24
ITV5	0176 259.13
CBM5D th. 0,5 mm	0173 530.24

(10) Sides of block (12) Top of block

Note : (1) A circuit separator SC may be required with the use of these accessories.
 (2) Use of these accessories requires the user to cut out the partition.
 (3) For block equipped with test socket AL2.