

LXD3B7

TeSys D - contactor coil - LXD3 - 24 V AC
50/60 Hz for 40... 65 A contactor

Main

Range of product	TeSys D
Product or component type	Contactor coil
Device short name	LXD3
Control circuit type	AC 50/60 Hz
Control circuit voltage	24 V AC 50/60 Hz
Average resistance	1.98 Ohm at 20 °C
Inductance of closed circuit	0.12 H
Product compatibility	LC1D40A...D65A LC1DT60A LC1DT80A
Operating time	4...19 ms opening 12...26 ms closing
Motor power HP (according to UL / CSA)	6 Mcycles
Operating rate	3600 cyc/h at ≤ 60 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.6 Uc at 60 °C drop-out 50/60 Hz 0.8...1.1 Uc at 60 °C operational 50 Hz 0.85...1.1 Uc at 60 °C operational 60 Hz
Inrush power in VA	160 VA at 20 °C (cos φ 0.75) 60 Hz 160 VA at 20 °C (cos φ 0.75) 50 Hz
Hold-in power consumption in VA	15 VA at 20 °C (cos φ 0.3) 60 Hz 15 VA at 20 °C (cos φ 0.3) 50 Hz
Heat dissipation	4...5 W at 50/60 Hz

Environment

Ambient air temperature for operation	-5...60 °C
Product weight	0.07 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.