

F

E

D

C

B

A

F




E

D

C

B

A



30.5	29.3	25.65	24.5	54132-5097	54132-5039	50
28.0	26.8	23.15	22.0	-4597	-4539	45
27.0	25.8	22.15	21.0	-4397	-4339	43
25.5	24.3	20.65	19.5	-4097	-4039	40
24.5	23.3	19.65	18.5	-3897	-3839	38
23.5	22.3	18.65	17.5	-3697	-3639	36
23.0	21.8	18.15	17.0	-3597	-3539	35
22.5	21.3	17.65	16.5	-3497	-3439	34
22.0	20.8	17.15	16.0	-3397	-3339	33
21.5	20.3	16.65	15.5	-3297	-3239	32
20.5	19.3	15.65	14.5	54132-3097	54132-3039	30
D	C	B	A	EMBOSSED TAPE ORDER No. オーダー番号	MATERIAL. NO.	CKT.

REVISED EC NO: J2008-4308 DRWN:MABEI 2008/06/27 CHKD:THARUYAMA 2008/06/30 APPR:NUKITA 2008/06/30 B	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	MODEL NO.		
				MM ONLY		---	METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY M.NABEI	DATE '03/12/15	TITLE 0.5 FPC CONN ZIF HOUSING ASSY FOR SMT -LEAD FREE-				
		10 OVER 30 UNDER	± 0.25	CHECKED BY M.SASAO	DATE '03/12/15					
		30 OVER	± 0.3	APPROVED BY M.SASAO	DATE '03/12/15	MOLEX INCORPORATED				
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE TABLE		SD-54132-060						1 OF 2
		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

F

E

D

C

B

A

F


E

D


C

B


A



参考基板レイアウト
RECOMMENDED PC BOARD PATTERN DIMENSION(REF.)
(マウント面)
(MOUNTING SIDE)



適合FPC推奨寸法
APPLICABLE FPC RECOMMENDED DIMENSION
(仕上がり厚さ: 0.3±0.03)
(THICKNESS: 0.3±0.03)



適合FFC推奨寸法
APPLICABLE FFC RECOMMENDED DIMENSION
(仕上がり厚さ: 0.3±0.03)
(THICKNESS: 0.3±0.03)

注記
NOTES

1. 使用材料
MATERIAL
ハウジング
HOUSING : 46ナイロン, UL94V-0
: 46NYLON
アクチュエーター
ACTUATOR : PPS, UL94V-0
: PPS
ターミナル
TERMINAL : リン青銅 (t=0.2), 鍍・ビスマスメッキ 1.0~3.0 MICRO METER MIN.
: ニッケル下地 1.0~3.0 MICRO METER MIN.
: PHOS-BRO, TIN-BISMUTH-PLATE 1.0~3.0 MICRO METER MIN.
OVER NICKEL 1.0~3.0 MICRO METER MIN.
金具
FITTING NAIL : リン青銅 (t=0.2), 鍍メッキ 1.0~3.0 MICRO METER MIN.
: ニッケル下地 1.0~3.0 MICRO METER MIN.
: PHOS-BRO, TIN-PLATE 1.0~3.0 MICRO METER MIN.
OVER NICKEL 1.0~3.0 MICRO METER MIN.

2. エンボステープ梱包時は、アクチュエーターがロックした状態とする。
IN THE PACKAGE, ACTUATOR OF PART NO.54132-***31
SHOULD BE LOCKED.
3. ソルダーテール半田付け面のスレ量、及び金具半田付け面のスレ量は、
基準面 田に対し上方向0.1MAX. 下方向0.15MAX. とする。
MISALIGNMENT OF SOLDER TAILS AND FITTING NAIL FROM 田
UPPER DIRECTION: 0.1 MAX., LOWER DIRECTION: 0.15 MAX.
4. 偶数極に適用
APPLY FOR EVEN CIRCUIT.
5. パターンはくり止め用金具
FITTING NAIL FOR PREVENTION OF PEELING
OF P.C.B. PATTERN.
6. 本製品は54132-***31の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 54132-***31

FPC/FFCについて

打抜き方向は導体側から補強板側を推奨いたします。
導体部については軟銅箔35マイクロメートルまたは50マイクロメートル
RECOMMENDED PUNCHER DIRECTION:
FROM CONDUCTOR SIDE TO STIFFENER BOARD SIDE.
RECOMMENDED CONDUCTOR SPEC.:
THICKNESS OF SOFT COPPER FOIL:
35 micrometer or 50 micrometer

REVISED		EC NO: J2008-4308		2008/06/27		DRWN: MNABE		2008/06/30		CHKD: THARUYAMA		2008/06/30		APPR: NUKITA		2008/06/30		REV	
GENERAL TOLERANCES (UNLESS SPECIFIED)		10 UNDER		±0.2		10 OVER 30 UNDER		±0.25		30 OVER		±0.3		ANGULAR		±3 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
DIMENSION STYLE MM ONLY		DRAWN BY		DATE		CHECKED BY		DATE		APPROVED BY		DATE		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
M. NABE		'03/12/15		M. SASAO		'03/12/15		M. SASAO		'03/12/15		SEE SHEET 1		SD-54132-060		2 OF 2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

DWG. NO.
SD-54132-061

F

D

Δ

C

B

DO NOT SCALE DRAWING

EC NO.
DRWN:
CH'K:
APPR:

EC NO.
DRWN:
CH'K:
APPR:

EC NO.
DRWN:
CH'K:
APPR:

REVISED
EC NO. J2004-2790
DRWN: H. SHIMABUKURO '04/32
CH'K: M. SASAO '04/32
APPR: M. SASAO '04/32




RELEASED
EC NO. J2004-1538
DRWN: M. NABEI '03/12/15
CH'K: M. SASAO '03/12/15
APPR: M. SASAO '03/12/15

REV DESCRIPTION

MATERIAL
材料
SHEET 1 OF 2 参照
REFER TO SHEET 1 OF 2
FINISH
仕上げ
WIRE RANGE
適用電線範囲
INS. RANGE
被覆外径

GENERAL TOLERANCES:
(UNLESS SPECIFIED)
一般公差
10 UNDER
未満
10 OVER
以上
30 UNDER
未満
30 OVER
以上
ANGLE 角度

54132-**97		MODEL.NO.		DIMENSIONS:		SHT	REV
SCALE ——//——	DESIGN UNITS ☒ mm ☐ INCH	 THIRD ANGLE PROJECTION		☐ $\frac{\text{mm}}{\text{INCH}}$	☐ $\frac{\text{INCH}}{\text{mm}}$	☒ mm ONLY	REVISE ON CAD ONLY
DRAWN BY & DATE M.NABEI '03/12/15		TITLE: EMBOSSED TAPE PACKAGE FOR 0.5 FPC CONN. ZIF -LEAD FREE-					
CHECKED BY & DATE M.SASAO '03/12/15							
APPROVED BY & DATE M.SASAO '03/12/15		MOLEX INCORPORATED					
CAD FILENAME SD-54132-061.S02		MATERIAL NO. SEE CHART		DRAWING NO. SD-54132-061		SHEET NO. 2 OF 2	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.							SIZE B



44	49.4	45.4	30.8	31.6	26.1	29.6	54132-5097	50	
			28.3	29.4	23.6	27.1	4	-4597	45
			27.3	28.4	22.6	26.1		-4397	43
			25.8	26.9	21.1	24.6		-4097	40
			24.8	25.9	20.1	23.6		-3897	38
			23.8	24.9	19.1	22.6		-3697	36
			23.3	24.4	18.6	22.1		-3597	35
			22.8	23.9	18.1	21.6		-3497	34
			22.3	23.4	17.6	21.1		-3397	33
			21.8	22.9	17.1	20.6	7	-3297	32
			20.8	21.9	16.1	19.6	54132-3097	30	
キャリアテープ幅 CARRIER TAPE WIDTH	F	E	D	C	B	A	ENG. NO.	CKT.	

8

7

6

5

4

3

2

EN-02J(097) MXJ-54

SD-54132-061.S02