





△ BODY-MATL: BRASS PER MIL-C-50.
FINISH: PLATED GOLD .000030 THK PER MIL-G-45204 FOR A LENGTH OF .200 MIN
FROM MATING END, .000100 MIN TIN-LEAD PER MIL-T-10727 IN WIRE BARREL
AREA, BOTH OVER NICKEL .000050 THK PER QQ-N-290.
SPRING-MATL: STAINLESS STEEL PER QQ-S-766.
POST-MATL: BRASS PER ASTM-B-134.
FINISH: PLATED MATTE TIN-LEAD PER MIL-T-10727 OVER NICKEL .000050 THK
PER QQ-N-290.

△ BODY-MATL: BRASS PER MIL-C-50.
FINISH: PLATED GOLD .000030 THK PER MIL-G-45204 FOR A LENGTH OF .200 MIN
FROM MATING END, .000100 MIN TIN PER MIL-T-10727 IN WIRE BARREL AREA,
BOTH OVER NICKEL .000050 THK PER QQ-N-290.
SPRING-MATL: STAINLESS STEEL PER QQ-S-766.
POST-MATL: BRASS PER ASTM-B-134.
FINISH: PLATED MATTE TIN PER MIL-T-10727 OVER NICKEL .000050 THK PER QQ-N-290.



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. HOFFECKER 5-12-86	Tyco Electronics Corporation Harriaburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK L. LAWVER 5-12-86	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		
1 PLC ± -		SIZE		
2 PLC ± -		CAGE CODE		
3 PLC ± .010		DRAWING NO		
4 PLC ± -		RESTRICTED TO		
ANGLES ± -		A1 00779		
FINISH		C=213289		
MATERIAL SEE CALLOUTS		WEIGHT		
SEE CALLOUTS		CUSTOMER DRAWING		
SCALE		2:1		
SHEET		1 of 1		
REV		L		

CONTACT FINISH	213289-2
	213289-1
PART NUMBER	