


PITTB 2,5-PE/L

Order No.: 3210978



Ground modular terminal block, Cross section: 0.14 mm² - 4 mm²,
AWG: 26 - 12, Connection type: Leg spring connection, Width: 5.2
mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Commercial data

EAN	4046356419048
Note	Made-to-order
Electrical Number	1264961
Pack	50
Customs tariff	85369010
country of origin	PL
Catalog page information	Page 187 (CL-2009)

[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General

Number of levels	2
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class acc. to UL 94	V0

Dimensions

Width	5.2 mm
-------	--------

Length	68 mm
Height NS 35/7,5	47.5 mm
Height NS 35/15	55 mm

Technical data

Rated surge voltage	6 kV
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1 / IEC 60947-7-2
Nominal current I_N	24 A
Nominal voltage U_N	500 V

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Type of connection	Leg spring connection
Stripping length	10 mm
Internal cylindrical gage	A3

Certificates / Approvals

CUL

Nominal voltage U_N	20 V
Nominal current I_N	300 A
AWG/kcmil	24-12

UL

Nominal voltage U_N	300 V
Nominal current I_N	20 A
AWG/kcmil	24-12

Accessories

Item	Designation	Description
------	-------------	-------------

Assembly

3030747	ATP-STTB 4	Partition plate, Length: 88.7 mm, Width: 2 mm, Height: 53 mm, Color: gray
3022276	CLIPFIX 35-5	Snap-on end bracket, for NS 35/7.5 or NS 35/15 DIN rail, can be fitted with Zack strip ZB 5 and ZBF 5, terminal strip marker KLM 2 and KLM, parking facility for FBS...5, FBS...6, KSS 5, KSS 6, width: 5,15 mm, color: gray
3036725	DP PS-5	Spacer plate, Color: red
3030459	D-STTB 2,5	End cover, Length: 67.5 mm, Width: 2.2 mm, Height: 47.5 mm, Color: gray
0801704	NS 35/ 7,5 AL UTEN HULL 2M	DIN rail, material: Aluminum, unperforated, height 7.5 mm, width 35 mm, length: 2 m
0801762	NS 35/ 7,5 CU UTEN HULL 2M	DIN rail, material: Copper, unperforated, height 7.5 mm, width 35 mm, length: 2 m
1208131	NS 35/ 7,5 HULLET/...	DIN rail, Color: silver
1207640	NS 35/ 7,5 HULLET 755MM	NS 35 DIN rail, height 7.5 mm, length 755 mm
1207666	NS 35/ 7,5 HULLET 1155MM	NS 35 DIN rail, height 7.5 mm, length 1155 mm
0801733	NS 35/ 7,5 HULLET 2M	DIN rail, material: Steel, galvanized and passivated with a thick layer, perforated, height 7.5 mm, width 35 mm, length: 2 m
1207653	NS 35/ 7,5 HULLET 955MM	NS35 DIN rail, height 7.5 mm, length 955 mm
1208115	NS 35/ 7,5 UTEN HULL/...	DIN rail, Color: silver
0801681	NS 35/ 7,5 UTEN HULL 2M	DIN rail, material: Steel, unperforated, height 7.5 mm, width 35 mm, length: 2 m
1208128	NS 35/ 7,5 UTEN HULL/SO/...	DIN rail, Color: silver
0801377	NS 35/ 7,5 V2A UTEN HULL 2M	DIN rail, Width: 35 mm, Height: 7.5 mm, Length: 2000 mm, Color: silver
1206421	NS 35/ 7,5 ZN HULLET 2M	DIN rail, material: Galvanized, perforated, height 7.5 mm, width 35 mm, length: 2 m
1206434	NS 35/ 7,5 ZN UTEN HULL 2M	DIN rail, material: Galvanized, unperforated, height 7.5 mm, width 35 mm, length: 2 m
1201895	NS 35/15 CU UTEN HULL 2M	DIN rail, material: Copper, unperforated, 1.5 mm thick, height 15 mm, width 35 mm, length: 2 m

1201730	NS 35/15 HULLET 2M	DIN rail, material: Steel, perforated, height 15 mm, width 35 mm, length: 2 m
1208144	NS 35/15 UTEN HULL/...	DIN rail, Color: silver
1201714	NS 35/15 UTEN HULL 2M	DIN rail, material: Steel, unperforated, height 15 mm, width 35 mm, length: 2 m
1208157	NS 35/15 UTEN HULL/SO/...	DIN rail, Color: silver
1206586	NS 35/15 ZN UTEN HULL 2M	DIN rail, material: Galvanized, unperforated, height 15 mm, width 35 mm, length: 2 m

Bridges

3030161	FBS 2-5	Plug-in bridge, Number of positions: 2, Color: red
3030174	FBS 3-5	Plug-in bridge, Number of positions: 3, Color: red
3030187	FBS 4-5	Plug-in bridge, Number of positions: 4, Color: red
3030190	FBS 5-5	Plug-in bridge, Number of positions: 5, Color: red
3030213	FBS 10-5	Plug-in bridge, Number of positions: 10, Color: red
3030226	FBS 20-5	Plug-in bridge, Number of positions: 20, Color: red
3038930	FBS 50-5	Plug-in bridge, Number of positions: 50, Color: red

Marking

0800967	STP 5-2	Double marker carrier, snaps onto the double-level spring-cage terminal block STTB 2.5 and STTB 4, labeled with ZB 5 or ZBF 5
0800970	STP 5-2/S	Double marker carrier, snaps onto the double-level spring-cage terminal block ZFKK 1,5, with MSTBV or ICV pick-off
0818108	UC-TM 5	UniCard sheets, for labeling terminal blocks using Zack marker strip groove, 96-section, labeling with BLUEMARK X1 and CMS-P1-PLOTTER, color: White
0824581	UC-TM 5 CUS	UniCard sheets, for labeling terminal blocks with a zack marker strip groove, can be printed as per customer requirements
0819796	UC-TMF 5L	UniCard sheets, for labeling terminal blocks using a flat Zack marker strip groove, 192-section, can be labeled with CMS-P1-PLOTTER, color: White

Plug/Adapter


3002843	ISH 2,5/0,2	Insulation stop sleeve, Color: white
3002856	ISH 2,5/0,5	Insulation stop sleeve, Color: gray
3002869	ISH 2,5/1,0	Insulation stop sleeve, Color: black
3030925	PAI-4	Test adapter, Color: gray
3030983	PS-5	Test adapter, Color: red

Tools

1204517	SZF 1-0,6X3,5	Screwdriver, blade: 0.6 x 3.5 x 100 mm, length 180 mm
---------	---------------	---

Diagrams/Drawings

Circuit diagram



Address

PHOENIX CONTACT AS
Strømsveien 344
N-1001 Oslo, Norway
Phone +47 22 07 68 00
Fax +47 22 07 68 10
<http://www.phoenixcontact.no>



© 2010 Phoenix Contact
Technical modifications reserved;