

**Crimping tool
PZ 1.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Order No.	9005990000
Type	PZ 1.5
Version	Crimping tool, Crimping tool for wire-end ferrules, 0.14 mm², 1.5 mm², Trapezoidal crimp
GTIN (EAN)	4008190085964
Qty.	1 pc(s).

Crimping tool
PZ 1.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions

Length	170 mm	Weight	170 g
Net weight	171.171 g		

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Contact description

Type of contact	Wire-end ferrules with/without plastic collars	Crimping range, min.	0.14 mm ²
Crimping range, max.	1.5 mm ²		

Tool data - crimping

Crimping type/profile	Trapezoidal crimp	Wire end ferrules cross-section, min.	0.25 mm ²
Wire end ferrules cross-section, max.	1.5 mm ²		

Classifications

ETIM 2.0	EC000168	ETIM 3.0	EC000168
UNSPSC	23-17-16-04	eClass 4.1	21-04-03-01
eClass 5.1	21-04-03-01	eClass 6.0	21-04-38-90
eClass 7.0	21-04-38-90		

Product information

Descriptive text ordering data	Additional accessories can be found in Chapter J
Descriptive text accessories	Information and ordering data for wire-end ferrules - see Chapter J Accessories wire-end ferrules
Description of article	Crimping tool for wire end ferrules with/without plastic collar, 0,14 bis 1,5 mm ²
Product description	• Only one die for the whole cross-section range • Crimp complies with Euro-Norm EN 60947-1 • Wire-end ferrule insertion from the front

Approvals

Approvals



Crimping tool
PZ 1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

