



Main

Range of product	TeSys D thermal overload relays
Product or component type	Differential thermal overload relay
Device short name	LR9D
Relay application	Motor protection
Product compatibility	LC1D115 LC1D150 NSX circuit breaker
Network type	AC
Overload tripping class	Class 10A conforming to IEC 60947-4-1 Class 10 conforming to IEC 60947-4-1
Signalling function	Alarm
Thermal protection adjustment range	90...150 A
[Ui] rated insulation voltage	600 V power circuit conforming to UL 600 V power circuit conforming to CSA 1000 V power circuit conforming to IEC 60947-4-1

Complementary

Network frequency	50...60 Hz
[Us] rated supply voltage	24 V DC
Supply voltage limits	17...32 V
Mounting support	Rail Direct on contactor
Tripping threshold	1.12 +/- 0.06 In de-energisation conforming to IEC 60947-4-1 1.05 +/- 0.06 In alarm conforming to IEC 60947-4-1
[Ith] conventional free air thermal current	5 A for signalling circuit
Associated fuse rating	5 A gG for signalling circuit
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 61000-4-5
Phase failure sensitivity	Tripping in 4 s +/- 20 % conforming to IEC 60947-4-1
Temperature compensation	-20...70 °C
Switching capacity in mA	0...150 mA
Voltage drop	<= 2.5 V closed state
Connections - terminals	Alarm circuit: screw clamp terminals 1 cable(s) 0.5...1.5 mm ² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable(s) 0.5...1.5 mm ² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable(s) 0.5...1.5 mm ² - cable stiffness: flexible - without cable end Power circuit: bars
Tightening torque	Control circuit: 1.2 N.m - on screw clamp terminals Power circuit: 18 N.m - on bars screw : M8 Alarm circuit: 0.45 N.m - on screw clamp terminals
Depth	132 mm
Product weight	0.885 kg
Quantity per set	Set of 10

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	EN 60947-4-1 IEC 255-17 IEC 255-8 IEC 60947-4-1 VDE 0660
Product certifications	CSA 22-2 UL 508
Protective treatment	TH
IP degree of protection	IP20 conforming to VDE 0106 IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...55 °C conforming to IEC 60255-8
Ambient air temperature for storage	-40...85 °C
Operating altitude	<= 2000 m without derating
Mechanical robustness	Shocks 13 Gn for 11 ms IEC 60068-2-7 Vibrations 2 Gn, 5...300 Hz IEC 60068-2-6
Dielectric strength	6 kV at 50 Hz conforming to 60255-5