

13 cm (5") HiFi-Deckenlautsprecher mit korrosionsbeständigem Abdeckgitter, geeignet für den Einbau in Unterdecken aller Materialien. Bestückt mit einem 2-Wege-Koaxiallautsprecher. Schnellmontage durch einen kreisrunden Unterdeckenausschnitt, in den der Lautsprecher mit Montagering in Snap-In-Technik eingesetzt wird. Der Anschluss sowie die eventuell notwendige Pegelanpassung im 100-V-Netz erfolgt durch eine einfach zu handhabende Druckfederklemme. Das formschöne Abdeckgitter wird mit einer Bajonettverbindung schnell und praktisch befestigt. Farbe: RAL 9010.


Auf Anfrage auch in anderen RAL-Farben erhältlich.

Lautsprecher-Gehäusesysteme für Betondecken zu diesem Lautsprecher liefert die Firma KAISER, 58579 Schalksmühle. Für unsere Deckenlautsprecher empfehlen wir die Gehäuse der KompaX-Baureihe, welche es in drei verschiedenen Ausführungen gibt. Je nach Bedarf sind zusätzliche Frontteile (Frontringe, Mineralfaserplatten etc.) notwendig. Genauere Informationen entnehmen Sie bitte der Homepage von KAISER (Einbaugesäuse für Leuchten und Lautsprecher). Durch Anklicken der "Technischen Informationen" des jeweiligen Produktes erhalten Sie weitere Details zum Einbau. Brandschutzstöpsel (F30) sind unter dem Namen FlamoX erhältlich.

13 cm (5") HiFi-ceiling speaker with corrosion free grille, suitable for the installation in suspended ceilings of any material. Equipped with a 2-way coaxial driver. Quick snap-in mounting due to round ceiling cut-out through which the speaker with mounting ring can be installed. A push-terminal block allows a quick and easy connection including the eventually necessary level adjustment to the 100-V-network. A quick-mounting bayonet connection provides an easy installation of the grille. Colour: RAL 9010.



Can be supplied painted in other RAL colours on request.

Speaker cabinet systems for concrete ceilings are available from KAISER, 58579 Schalksmühle, Germany. The KompaX cabinet series is suitable for our ceiling speakers. Some additional front parts maybe necessary (front rings, mineral fibreboard etc.). More details are available on the Homepage of KAISER (Housing for lamps and loudspeakers). In order to get more detailed information, press the "Technical information" button of the particular product. Fire protection housing systems (F30) are also available (FlamoX).



DL 13/2 - 100 V
18.03.2008

DL 13/2 - 100 V



Technische Daten / Technical Data

Trafoanpassung	6; 3; 1,5 W
Transformer matching	
Schalldruckpegel	98 dB (1 W/1 m)
Sound pressure level	@ 5000 Hz
Abstrahlwinkel (-6 dB)	52° / 4000 Hz
Opening angle (-6 dB)	
Übertragungsbereich (-10 dB)	100-20000 Hz
Frequency response (-10 dB)	
Mittlerer Schalldruckpegel	89 dB (1 W/1 m)
Mean sound pressure level	
Max. Schalldruckpegel	96 dB (6 W/1 m)
Max. sound pressure level	
Schwingspulendurchmesser	25 mm Ø
Voice coil diameter	
Schallwandöffnung	165 mm Ø
Cut-out diameter	
Farbe	RAL 9010
Colour	
Gewicht netto	1,015 kg
Net weight	