



## Rotary lever, metal

**Part no.**  
**Article no.**  
**Catalog No.**

**LSM-XRL**  
**266159**  
**LSM-XRL**



Powering Business Worldwide™

### Delivery programme

Basic function		Operating heads
Part group reference		LS(M)-...
Product range		Rotary lever
Design		EN 50047 Form A
For use with		Basic devices LS(M)...
<b>Notes</b> The operating head can be rotated at 90° intervals to adapt to the specified approach direction.		

### Approvals

Product Standards  
UL File No.  
UL Category Control No.  
CSA File No.  
CSA Class No.  
North America Certification

IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking  
E29184  
NKCR  
12528  
3211-03  
UL listed, CSA certified

### Technical data ETIM 5.0

Sensors (EG000026) / Drive head for position switches/hinge switches (EC001483)		
Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Drive head for position switches (ecl@ss8-27-27-06-04 [BAA083008])		
Type of control element		Rotary lever

### Dimensions

