

## RefLED MR16

RefLED MR16 5.5W 345LM 830 36° SL

**0026634**



### Range features

### PRODUCT OVERVIEW

Ordering number	26634
Technology	LED
Light colour	830 Warm White
Energy class	A+
Average life (Rated) (h)	20000
Lamp shape	Reflector
Lamp finish	White
Dimmable	No
Cap/Base	GU5.3
Type	RefLED MR16
CRI (Ra)	80
Beam angle(°)	36
Colour temperature (K)	3000
Useful luminous flux (Rated) (lm)	345
Efficacy (Rated) (lm/w)	63
Watt (Nominal) (W)	5.5
Equivalent watt (W)	35
Voltage (V)	12

# RefLED MR16

RefLED MR16 5.5W 345LM 830 36° SL

**0026634**

## DATA TABLE

### General data

Ordering number	26634
Technology	LED
Average life (Nominal) (h)	15000
Energy class	A+
Average life (Rated) (h)	20000
Energy saving lamp	Yes
Lamp shape	Reflector
Lamp finish	White
Dimmable	No
Cap/Base	GU5.3
Type	RefLED MR16
Product name	RefLED MR16 5.5W 345LM 830 36° SL
Lamp mercury content (mg)	0
Starting time (max) (s)	<0,5
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	20000
Special purpose lamp	No
Transformer required	Yes
Optimal operating condition (°C)	25

### Optical data

Light colour	830 Warm White
CRI (Ra)	80
Suitable for accent lighting	Yes
Beam angle (Rated) (°)	36
Beam angle(°)	36
Colour temperature (K)	3000
Colour Consistency	6
Useful luminous flux (Rated) (lm)	345
Lumen maintenance at end of nominal life (%)	85
Peak intensity (cd)	950
Chromaticity coordinate Y	-1
Chromaticity coordinate X	-1
Adjustable chromaticity	No

## RefLED MR16

*RefLED MR16 5.5W 345LM 830 36° SL*

**0026634**

### Electrical data

<b>kWh per 1000 hours burning time</b>	6
<b>Efficacy (Rated) (lm/w)</b>	63
<b>Watt (Nominal) (W)</b>	5.5
<b>Watt (Rated) (W)</b>	5.5
<b>Equivalent watt (W)</b>	35
<b>Voltage (V)</b>	12
<b>Current (A)</b>	0.650
<b>Lamp power factor</b>	0.70

### Physical data

<b>Lamp Length (mm) - C/L</b>	46
<b>Max. Lamp Diameter (mm) - D</b>	50
<b>Lamp dimension equal to filament lamp equivalent</b>	Yes
<b>Designed for optimum use in non standard conditions</b>	No
<b>Fluorescent lamp replacement</b>	No