






LOC		DIST		REVISIONS						
CM		53		P	LTR	DESCRIPTION		DATE	DWN	APVD
					U1	REVISED PER ECO-11-004917		11MAR11	RK	HMR


 NICKEL OVER ENTIRE TERMINAL WITH 0.00076 THICK GOLD OVER 5.08 LENGTH.



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1




SECTION C-C
SCALE 10:1

1.50	.059	2.41	.095	-	-
1.27	.050	2.29	.090	16.89	.665
0.76	.030	2.16	.085	5.08	.200
0.20	.008	2.08	.082	3.68	.145
0.13	.005	1.91	.075	3.30	.130
0.00076	0.00030	1.57	.062	2.79	.110
MM	IN	MM	IN	MM	IN

CONVERSION TABLE

PRE-TIN	0.20 PH BRZ	1.27 - 2.79	0.2 - 0.9 mm ² (24-18 AWG)	350629-8
	0.20 BRASS	1.27 - 2.79	0.2 - 0.9 mm ² (24-18 AWG)	350629-5
PRE-TIN	0.20 BRASS	1.27 - 2.79	0.2 - 0.9 mm ² (24-18 AWG)	350629-1
FINISH	MATERIAL	INSULATION DIAMETER	WIRE RANGE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS 9-12-90	 TE Connectivity	
		CHK R. SWING 9-13-90		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME .062 PIN, COMMERCIAL PIN AND SOCKET	
		0. PLC ± -	SIZE A1	
		1. PLC ± -	CAGE CODE 00779	
		2. PLC ± -	DRAWING NO 350629	
		3. PLC ± 0.13	RESTRICTED TO -	
		4. PLC ± -		
MATERIAL SEE TABLE		ANGLES SEE TABLE	WEIGHT -	
			CUSTOMER DRAWING	
			SCALE 8:1	
			SHEET 1 OF 1	
			REV U1	