

Price* : 22.86 GBP



Main

Range	TeSys
Product or component type	Auxiliary contact block
Product compatibility	GV7RE GV7RS

Complementary

Auxiliary contacts operation	Standard
Pole contact composition	1 C/O
[Ui] rated insulation voltage	690 V - for control circuit - conforming to IEC 60947-1
[Ue] rated operational voltage	110 V AC for control circuit 110 V DC for control circuit 230...240 V AC for control circuit 24 V AC for control circuit 24 V DC for control circuit 250 V DC for control circuit 380...415 V AC for control circuit 440 V AC for control circuit 48 V AC for control circuit 48 V DC for control circuit 690 V AC for control circuit
Mechanical durability	50000 cycles
Minimum switching current	5 mA for control circuit
Minimum switching voltage	17 V for control circuit
Connections - terminals	Control circuit : connector 1 cable 1.5 mm ² - cable stiffness: flexible - with cable end Control circuit : connector 1 cable 1.5 mm ² - cable stiffness: flexible - without cable end Control circuit : connector 1 cable 1.5 mm ² - cable stiffness: solid
Product weight	0.015 kg

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0744 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---------------------------------------------------------------------------------------------------------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------