



Main

Range	TeSys
Device short name	LU6MB
Product or component type	Reverser block

Complementary

Mounting mode	Rail
[Ue] rated operational voltage	230 V 440 V 500 V 690 V
Network frequency	40...60 Hz
Inrush restraint duration	15 ms for DC network 25 ms for AC network 50/60 Hz
Operating time	150 ms with change of direction 75 ms without change of direction
[Uc] control circuit voltage	24 V DC
Current consumption	120 mA at 24 V DC maximum while closing 120 mA at 24 V DC rms sealed
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 600 V conforming to UL 508 690 V conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-6-2
Connections - terminals	Control circuit : screw clamp terminals 1 cable 0.34...1.5 mm ² - external diameter: 3 mm - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable 0.75...1.5 mm ² - external diameter: 3 mm - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable 0.75...1.5 mm ² - external diameter: 3 mm - cable stiffness: rigid - without cable end Control circuit : screw clamp terminals 2 cable 0.34...1.5 mm ² - external diameter: 3 mm - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 2 cable 0.75...1.5 mm ² - external diameter: 3 mm - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable 0.75...1.5 mm ² - external diameter: 3 mm - cable stiffness: rigid - without cable end Power circuit : screw clamp terminals 1 cable 1...10 mm ² - external diameter: 4 mm - cable stiffness: rigid - without cable end Power circuit : screw clamp terminals 1 cable 1...6 mm ² - external diameter: 4 mm - cable stiffness: flexible - with cable end

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Power circuit : screw clamp terminals 1 cable 2.5...10 mm² - external diameter: 4 mm - cable stiffness: flexible - without cable end
 Power circuit : screw clamp terminals 2 cable 1...6 mm² - external diameter: 4 mm - cable stiffness: flexible - with cable end
 Power circuit : screw clamp terminals 2 cable 1...6 mm² - external diameter: 4 mm - cable stiffness: rigid - without cable end
 Power circuit : screw clamp terminals 2 cable 1.5...6 mm² - external diameter: 4 mm - cable stiffness: flexible - without cable end

Tightening torque	Control circuit : 0.8...1.2 N.m - with screwdriver 5 mm flat Power circuit : 1.9...2.5 N.m - with screwdriver 6 mm flat Power circuit : 1.9...2.5 N.m - with screwdriver 6 mm Philips No 2 Control circuit : 0.8...1.2 N.m - with screwdriver 5 mm Philips No 2
Product weight	0.425 kg

Environment

Standards	CSA C22.2 No 14 type E EN 60947-6-3 IEC 60947-6-3 UL 508 type E with phase barrier
Product certifications	ATEX DNV BV GL LROS (Lloyds register of shipping) UL ABS CSA GOST CCC ASEFA
IP degree of protection	IP20 front panel and wired terminals conforming to IEC 60947-1 IP20 other faces conforming to IEC 60947-1 IP40 front panel outside connection zone conforming to IEC 60947-1
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-25...60 °C with LUCM -25...70 °C with LUCA, LUCB, LUCC, LUCD
Fire resistance	650 °C conforming to IEC 60695-2-12 960 °C parts supporting live components conforming to IEC 60695-2-12
Operating altitude	2000 m
Shock resistance	10 gn power poles open conforming to IEC 60068-2-27 15 gn power poles closed conforming to IEC 60068-2-27
Vibration resistance	2 gn 5...300 Hz power poles open conforming to IEC 60068-2-27 4 gn 5...300 Hz power poles closed conforming to IEC 60068-2-27
Resistance to electrostatic discharge	8 kV level 3, in open air conforming to IEC 61000-4-2 8 kV level 4, on contact conforming to IEC 61000-4-2
Resistance to radiated fields	10 V/m level 3 conforming to IEC 61000-4-3
Resistance to fast transients	2 kV class 3 serial link conforming to IEC 61000-4-4 4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4
Immunity to radioelectric fields	10 V conforming to IEC 61000-4-6

Contractual warranty

Warranty period	18 months
-----------------	-----------