





NOTA / NOTE :

- CDC CONNECTIQUE PSA : No 9629966099 .
- PSA SPECIFICATION: 14: No 9629966099 .
- PLAN D'INTERFACE : TE Connectivity No 1544681 .
 - : PSA STE No 9638276999
- INTERFACE DRAWING : TE Connectivity No 1544681 .
 - : PSA STE No 9638276999
- PLAN D'ALVEOLE : TE Connectivity No : 1544995 .
 - : PSA STE No 9641756399
- CAVITY DRAWING : TE Connectivity No : 1544995 .
 - : PSA STE No 9641756399
- CAHIER DE PRECONISATIONS : TE Connectivity No 411-15697 .
 - : PSA STE No 9641781799
- UTILIZATIONS FILE : TE Connectivity No 411-15697 .
 - : PSA STE No 9641781799
- MSP : COTES SUIVIES EN MSP 1 / SPC DIMENSIONS .



REFERENCES PRO-COM /		TE Connectivity		pour CABLEURS	
PRONER /		TE Connectivity P/N for		WIRING MANUFACTURER	
COMPOSANTS	REFERENCES			MATIERE	COULEUR
	PART NUMBERS			MATERIAL	COLOR
Longuette 1 Tab 8mm NG1 Section 3 à 6 mm2 Wire section 3 to 6 mm2	P790861 (2) 1544332-1 (3)			Laiton pré-établé Pre-lined brass	1
Longuette 1 Tab 8mm NG1 Section 7 à 10 mm2 Wire section 7 to 10 mm2	P790862 (2) 1544333-1 (3)			Laiton pré-établé Pre-lined brass	1
Joint unifié à serlier Single wire seal Section 3 à 6 mm2 Wire section 3 to 6 mm2	P8010489526 (2) 1544316-1 (3)			Silicone 50sh A autolubrifié Silicone 50sh A self-lubricated	VERT Green
Joint unifié à serlier Single wire seal Section 7 à 10 mm2 Wire section 7 to 10 mm2	P8010589526 (2) 1544316-2 (3)			Silicone 50sh A autolubrifié Silicone 50sh A self-lubricated	ORANGE Orange
Bouchon Bundle	P8010689526 (2) 1544316-3 (3)			Silicone 50sh A non-lubrifié Silicone 50sh A no-lubricated	BLANC White

REFERENCES PRO-COM / TE CONNECTIVITY ET CODAGES COULEURS ASSOCIES		ET CODAGES COULEURS ASSOCIES
PRONER COMATEL / TE Connectivity P/N		AND ASSOCIATED CODING COLOR
P8010389536 02	P8010389536 04	P8010389536 06
1544334-1	1544334-2	1544334-3
NOIR / BLACK	BLEU / BLUE	GRIS / GREY

(2) : REF / PN PRONER COMATEL
(3) : REF / PN TE CONNECTIVITY

CARACTERISTIQUES MECANQUES CDC PSA PSA MECHANICAL SPECIFICATIONS	VALEURS RESULTS
EFFORT D'INSERTION LANGUETTE / ALVEOLE (AVEC JOINT) : F < 35N TAB / CAVITY MATING FORCE (WITH SEAL) : F < 35N	27 N MAXI 27 N MAXI
EFFORT DE FERMETURE DU DV : 20N<F<40N SECONDARY LOCK CLOSING FORCE : 20N<F<40N	39 N MAXI 39 N MAXI
EFFORT D'ACCOUPLEMENT PC/PL : F < 80N REC HOUSING / TAB HOUSING CONNECTION FORCE : F < 80N	73 N MAXI 73 N MAXI

B	I	GRILLE DE DETECTION (DV) <i>Detection Grid (DV)</i>	PBT GF-10	JAUNE <i>Yellow</i>
A	I	PORTE-LANGUETTE <i>Tab Housing</i>	PBT GF-10	VOIR TABLEAU <i>See table</i>
Rep	Qté	DESIGNATION <i>Description</i>	MATIERE <i>Material</i>	COULEUR <i>Color</i>

[illegible]