


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		V1	REVISED PER ECO-11-004820	11MAR11	RK	HMR



- 1

1.27 μ m [.000050] MIN TIN-LEAD OVER
1.27 μ m [.000050] MIN NICKEL.
- 2

0.76 μ m [.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN OVER 1.27 μ m [.000050] MIN NICKEL PLATE. GOLD FLASH ALL OVER. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENT APPLICATIONS).
- 3

BRASS PER MIL-C-50.
- 4

PHOSPHOR BRONZE PER QQ-B-750.
- 5

WIRE RANGE 14-18 AWG.
- 6

INSULATION RANGE 2.79[.110]-3.81[.150] DIA.
- 7

0.38 μ m [.000015] MIN GOLD PER MIL-G-45204 IN LOCALIZED PLATE AREA, 1.27 μ m [.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER 1.27 μ m [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.
- 8

1.27 μ m [.000050] MIN TIN OVER
1.27 μ m [.000050] MIN NICKEL.
- 9

CU-NI ALLOY

OBSOLETE OBSOLETE OBSOLETE	SMALL PACK	3	8	66597-8	1-66602-1
	STANDARD	9	8	1-66597-1	1-66602-0
	STANDARD	9	2	1-66597-0	66602-9
	STANDARD	3	8	66597-8	66602-8
	SMALL PACK	3	2	66597-2	66602-7
	SMALL PACK	3	1	66597-1	66602-6
	STANDARD	3	7	66597-7	66602-5
	STANDARD	4	2	66597-5	66602-4
OBSOLETE	STANDARD	4	1	66597-4	66602-3
	STANDARD	3	2	66597-2	66602-2
	STANDARD	3	1	66597-1	66602-1
	MATERIAL	MATERIAL	FINISH	STRIP P/N REF	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN H MOLL 10-2-90	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK J.MCCLINTON 12-15-90	
		0 PLC $\pm$ -		APVD A.BOUILLIANNE 12-10-90	
		1 PLC $\pm$ -		PRODUCT SPEC	
		2 PLC $\pm$ 0.13[.005]		APPLICATION SPEC	
		3 PLC $\pm$ -		WEIGHT -	
		4 PLC $\pm$ -		CUSTOMER DRAWING	
		FINISH		SCALE 8:1	
MATERIAL		FINISH		SHEET 1 OF 1	
SPRING: SSTL		PIN BODY:SEE TBL		REV V1	