

## Classic Eco Candle

Cl.Ec Can Class C 28w E14 240v

**0023484**



### Range features

- 1:1 replacement of Incandescent Candle lamp
- More efficient - more savings
- Up to two times more average life compared to incandescent lamps = 2000 hours
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Sparkling light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- 100% dimmable



### PRODUCT OVERVIEW

Light colour	0
Technology	Halogen
Ordering number	0023484
Average life (Rated) (h)	2000
Energy class	D
Lamp shape	Candle
Lamp finish	Clear
Dimmable	Yes
Cap/Base	E14
Type	Candle ECO
EAN code	5410288234847
CRI (Ra)	100
Colour temperature (K)	2800
Useful luminous flux (Rated) (lm)	370
Watt (Nominal) (W)	28
Equivalent watt (W)	37
Voltage (V)	240

# Classic Eco Candle

Cl.Ec Can Class C 28w E14 240v

**0023484**

## DATA TABLE

### General data

<b>Ordering number</b>	0023484
<b>Technology</b>	Halogen
<b>Average life (Nominal) (h)</b>	2000
<b>Average life (Rated) (h)</b>	2000
<b>Energy saving lamp</b>	No
<b>Energy class</b>	D
<b>Lamp shape</b>	Candle
<b>Lamp finish</b>	Clear
<b>Dimmable</b>	Yes
<b>Cap/Base</b>	E14
<b>Type</b>	Candle ECO
<b>EAN code</b>	5410288234847
<b>E-number SE</b>	8355572
<b>E-number FI</b>	4740153
<b>Long description</b>	1:1 replacement of Incandescent Candle lamp. More efficient - more savings. Up to two times more average life compared to incandescent lamps = 2000 hours. Excellent colour rendering (CRI = 100). Instant illumination. Sparkling light output. Less heat generation than incandescent lamp. Less CO2 emissions. Identical shape as standard incandescent lamp. Commercial and domestic application. 100% dimmable
<b>Product name</b>	Cl.Ec Can Class C 28w E14 240v
<b>Lamp mercury content (mg)</b>	0
<b>Starting time (max) (s)</b>	0.01
<b>Warm-up time to 60% of full light (max) (s)</b>	Instant full light
<b>Control gear required</b>	No
<b>Fixture rating</b>	Open
<b>IEC Reference</b>	IEC 60357
<b>IEC Reference 2</b>	IEC 60432-2
<b>Intended purpose</b>	General lighting
<b>No. of switching cycles before premature failure (min)</b>	> 8000
<b>Special purpose lamp</b>	No
<b>Transformer required</b>	No
<b>Sales pack quantity</b>	10
<b>Optimal operating condition (°C)</b>	25

# Classic Eco Candle

*Cl.Ec Can Class C 28w E14 240v*

**0023484**

## Optical data

Light colour	0
CRI (Ra)	100
Suitable for accent lighting	No
Colour temperature (K)	2800
Useful luminous flux (Rated) (lm)	370
Lumen maintaining at end of nominal Life (lm)	80
Luminous flux (Nominal) (lm)	370

## Electrical data

Watt (Rated) (W)	28
Equivalent watt (W)	37
Watt (Nominal) (W)	28
Voltage (V)	240
Lamp power factor	1

## Physical data

Lamp included	No
Lamp Length (mm) - C/L	100
Lamp Diameter (mm) - D	36
Packaging outer width (cm)	38
Packaging outer length (cm)	108
Packaging outer height (cm)	31
Packaging single width (cm)	3.55
Packaging single length (cm)	3.55
Packaging single height (cm)	10.1

## Classic Eco Candle

*Cl.Ec Can Class C 28w E14 240v*

**0023484**

### TECHNICAL DRAWINGS

---

