

LP1D40008BW

TeSys D contactor - 4P(2 NO + 2 NC) - AC-1 -
≤ 440 V 60 A - 24 V DC coil



Main

| | |
|---|--|
| Range of product | TeSys D |
| Product or component type | Contacteur |
| Device short name | LP1D |
| Contacteur application | Resistive load |
| Utilisation category | AC-1 |
| Poles description | 4P |
| Power pole contact composition | 2 NO + 2 NC |
| [Ue] rated operational voltage | ≤ 690 V AC 25...400 Hz for power circuit ≤ 690 V DC for power circuit |
| [Ie] rated operational current | 60 A (≤ 60 °C) at ≤ 440 V AC AC-1 for power circuit |
| Control circuit type | DC wide range |
| Control circuit voltage | 24 V DC |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947 |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 60 A at ≤ 60 °C for power circuit |
| Irms rated making capacity | 800 A at 440 V for power circuit conforming to IEC 60947 |
| Rated breaking capacity | 800 A at 440 V for power circuit conforming to IEC 60947 |
| [Icw] rated short-time withstand current | 72 A ≤ 40 °C 10 min power circuit 165 A ≤ 40 °C 1 min power circuit 320 A ≤ 40 °C 10 s power circuit 720 A ≤ 40 °C 1 s power circuit |
| Associated fuse rating | 80 A gG at ≤ 690 V coordination type 1 for power circuit 80 A gG at ≤ 690 V coordination type 2 for power circuit |
| Average impedance | 1.5 mOhm at 50 Hz - Ith 60 A for power circuit |
| [Ui] rated insulation voltage | 690 V for power circuit conforming to IEC 60947-4-1 600 V for power circuit certifications CSA 600 V for power circuit certifications UL |
| Power dissipation per pole | 5.4 W AC-1 |
| Safety cover | Without |
| Mounting support | Plate Rail |
| Standards | EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 CSA C22.2 n°14 |
| Product certifications | BV CCC CSA DNV GL GOST RINA UL LROS |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|----------------------------------|---|
| Connections - terminals | <p>Power circuit: screw clamp terminals 1 cable(s) 1...35 mm² - cable stiffness: flexible - without cable end</p> <p>Power circuit: screw clamp terminals 2 cable(s) 1...25 mm² - cable stiffness: flexible - without cable end</p> <p>Power circuit: screw clamp terminals 1 cable(s) 1...35 mm² - cable stiffness: flexible - with cable end</p> <p>Power circuit: screw clamp terminals 2 cable(s) 1...25 mm² - cable stiffness: flexible - with cable end</p> <p>Power circuit: screw clamp terminals 1 cable(s) 1...35 mm² - cable stiffness: solid - without cable end</p> <p>Power circuit: screw clamp terminals 2 cable(s) 1...25 mm² - cable stiffness: solid - without cable end</p> <p>Control circuit: screw clamp terminals 1 cable(s) 1...4 mm² - cable stiffness: flexible - without cable end</p> <p>Control circuit: screw clamp terminals 2 cable(s) 1...4 mm² - cable stiffness: flexible - without cable end</p> <p>Control circuit: screw clamp terminals 1 cable(s) 1...4 mm² - cable stiffness: flexible - with cable end</p> <p>Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm² - cable stiffness: flexible - with cable end</p> <p>Control circuit: screw clamp terminals 1 cable(s) 1...4 mm² - cable stiffness: solid - without cable end</p> <p>Control circuit: screw clamp terminals 2 cable(s) 1...4 mm² - cable stiffness: solid - without cable end</p> |
| Tightening torque | <p>Power circuit: 5 N.m - on screw clamp terminals - cable ≤ 25 mm² hexagonal 4 mm</p> <p>Power circuit: 8 N.m - on screw clamp terminals - cable 25...35 mm² hexagonal 4 mm</p> <p>Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm</p> <p>Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2</p> |
| Operating time | <p>4...19 ms opening</p> <p>12...26 ms closing</p> |
| Safety reliability level | <p>B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1</p> <p>B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1</p> |
| Mechanical durability (millions) | 10 Mcycles |
| Operating rate | 3600 cyc/h at ≤ 60 °C |

Complementary

| | |
|--------------------------------|---|
| Coil technology | Built-in bidirectional peak limiting diode suppressor |
| Control circuit voltage limits | <p>0.1...0.3 U_c at 55 °C drop-out</p> <p>0.75...1.2 U_c at 55 °C operational</p> |
| Time constant | 75 ms |
| Inrush power in W | 22 W at 20 °C |
| Hold-in power consumption in W | 22 W at 20 °C |

Environment

| | |
|---|---|
| IP degree of protection | IP2x front face conforming to IEC 60529 |
| Protective treatment | TH conforming to IEC 60068-2-30 |
| Pollution degree | 3 |
| Ambient air temperature for operation | -5...60 °C |
| Ambient air temperature for storage | -60...80 °C |
| Permissible ambient air temperature around the device | -40...70 °C at U _c |
| Operating altitude | 3000 m without derating in temperature |
| Fire resistance | 850 °C conforming to IEC 60695-2-1 |
| Flame retardance | V1 conforming to UL 94 |
| Mechanical robustness | <p>Vibrations contactor open 2 Gn, 5...300 Hz</p> <p>Vibrations contactor closed 4 Gn, 5...300 Hz</p> <p>Shocks contactor open 10 Gn for 11 ms</p> <p>Shocks contactor closed 15 Gn for 11 ms</p> |

| | |
|----------------|---------|
| Height | 127 mm |
| Width | 85 mm |
| Depth | 125 mm |
| Product weight | 2.21 kg |