

Ordering number C12041_EVA-S

Family	Eva	FWHM	13 degrees
Type	Lens	Efficiency	94 %
LED	XM-L	cd/Im	-
Color	Clear	Gerber File	Available
Diameter	35 mm		
Height	16.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		

Outer flange can be secured in fixture for hardware-free attachment

Ordering number CA12055_EVA-S

Family	Eva	FWHM	13 degrees
Type	Assembly	Efficiency	92 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17.2 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, tape		
Status	Ready		

Ordering number CP12196_EVA-S

Family	Eva	FWHM	13 degrees
Type	Assembly	Efficiency	94 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, glue		
Status	Ready		

Ordering number C12828_EVA-O

Family	Eva	FWHM	15.5+39 degrees
Type	Lens	Efficiency	86 %
LED	XM-L	cd/Im	3.300
Color	Clear	Gerber File	Available
Diameter	35 mm		
Height	16.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		

**Ordering number CA12859_EVA-O**

Family	Eva	FWHM	15.5+39 degrees
Type	Assembly	Efficiency	86 %
LED	XM-L	cd/Im	3.300
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17.2 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Tape		
Status	Ready		

**Ordering number CP12860_EVA-O**

Family	Eva	FWHM	15.5+39 degrees
Type	Assembly	Efficiency	86 %
LED	XM-L	cd/Im	3.300
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw		
Status	Ready		

**Ordering number C10684_EVA-D**

Family	Eva	FWHM	16 degrees
Type	Lens	Efficiency	91 %
LED	XM-L	cd/Im	-
Color	Clear	Gerber File	Available
Diameter	35 mm		
Height	16.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		

Outer flange can be secured in fixture for hardware-free attachment

**Ordering number CA12057_EVA-D**

Family	Eva	FWHM	16 degrees
Type	Assembly	Efficiency	90 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17.2 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, tape		
Status	Ready		

**Ordering number CP12197_EVA-D**

Family	Eva	FWHM	20 degrees
Type	Assembly	Efficiency	91 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, glue		
Status	Ready		

**Ordering number C10685_EVA-M**

Family	Eva	FWHM	24 degrees
Type	Lens	Efficiency	88 %
LED	XM-L	cd/Im	-
Color	Clear	Gerber File	Available
Diameter	35 mm		
Height	16.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		

Outer flange can be secured in fixture for hardware-free attachment

**Ordering number CA12058_EVA-M**

Family	Eva	FWHM	24 degrees
Type	Assembly	Efficiency	89 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17.2 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, tape		
Status	Ready		

**Ordering number CP12198_EVA-M**

Family	Eva	FWHM	24 degrees
Type	Assembly	Efficiency	88 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, glue		
Status	Ready		

**Ordering number C10686_EVA-W**

Family	Eva	FWHM	40 degrees
Type	Lens	Efficiency	79 %
LED	XM-L	cd/Im	-
Color	Clear	Gerber File	Available
Diameter	35 mm		
Height	16.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		

Outer flange can be secured in fixture for hardware-free attachment

**Ordering number CA12059_EVA-W**

Family	Eva	FWHM	40 degrees
Type	Assembly	Efficiency	83 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17.2 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, tape		
Status	Ready		

**Ordering number CP12199_EVA-W**

Family	Eva	FWHM	40 degrees
Type	Assembly	Efficiency	79 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, glue		
Status	Ready		

**Ordering number C10909_EVA-WW**

Family	Eva	FWHM	64 degrees
Type	Lens	Efficiency	77 %
LED	XM-L	cd/Im	-
Color	Clear	Gerber File	Available
Diameter	35 mm		
Height	16.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		

Outer flange can be secured in fixture for hardware-free attachment

**Ordering number CA12060_EVA-WW**

Family	Eva	FWHM	64 degrees
Type	Assembly	Efficiency	79 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17.2 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, tape		
Status	Ready		

**Ordering number CP12200_EVA-WW**

Family	Eva	FWHM	64 degrees
Type	Assembly	Efficiency	77 %
LED	XM-L	cd/Im	-
Color	Black	Gerber File	Available
Diameter	37.7 mm		
Height	17 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Screw, glue		
Status	Ready		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Eva series

last update 20/12/2012

GENERAL INFORMATION

- Product series especially designed & optimized for XM-L series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.


Please find more information about used material from below:


http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

- Optic holder molded by high quality PC material (120 degrees of Celcius / 248 degrees of Fahrenheit).

Relative intensity of CA12059_Eva-W-XM-Tape





This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.



Ledil Oy
Salorankatu 10
24100 SALO
Finland

DRAWING TITLE

Datasheet Eva Spot Lens

DRAWN BY
ah

DATE
1.3.2013

CHECKED BY

DATE

SIZE
A4

DRAWING NUMBER

C12041

REV
1

DESIGNED BY
HH

DATE
26.08.2008

SCALE


2:1

WEIGHT (g)


SHEET

1 / 1


Luminaire: LEDIL OY C12828_EVA-O (XM-L) Efficiency=86%
Lamps: 1 x Cree XM-L (111lm @ 250mA)




Luminaire: LEDIL OY CA12859_EVA-O / CP12860_EVA-O (XM-L) Efficiency=86%
Lamps: 1 x Cree XM-L (1111lm @ 250mA)



Luminaire: LEDIL OY CA12859_EVA-O / CP12860_EVA-O (XM-L) Efficiency=86%
Lamps: 1 x Cree XM-L (1111lm @ 250mA)



Luminaire: LEDIL OY C12828_EVA-O (XM-L) Efficiency=86%
Lamps: 1 x Cree XM-L (111lm @ 250mA)




cd/klm

— C0 - C180

— C90 - C270

Luminaire: LEDIL OY CA12859_EVA-O / CP12860_EVA-O (XM-L) Efficiency=86%
Lamps: 1 x Cree XM-L (111lm @ 250mA)



Luminaire: LEDIL OY CA12859_EVA-O / CP12860_EVA-O (XM-L) Efficiency=86%
Lamps: 1 x Cree XM-L (111lm @ 250mA)

