



Main

Range of product	TeSys GC
Product or component type	Contacteur
Device short name	Modular standard contactor
Contacteur application	Heating Motor control
Utilisation category	AC-7B AC-7A
Control circuit type	AC
Poles description	2P
Pole contact composition	1 NO + 1 NC
[Uc] control circuit voltage	24 V AC 50 Hz
[Ith] conventional free air thermal current	40 A at <= 50 °C for power circuit 5 A at <= 50 °C for auxiliary contact

Complementary

Coil technology	Without built-in
Auxiliary contacts type	Type integrated in coil (1 NO)
Auxiliary contact composition	1 NO
Control circuit voltage limits	0.2...0.75 Uc at <= 50 °C drop-out 50 Hz 0.85...1.1 Uc at <= 50 °C operational 50 Hz
[Ui] rated insulation voltage	500 V for auxiliary contacts conforming to IEC 60947-5 500 V for power circuit conforming to VDE 0110 500 V for power circuit conforming to IEC 61095 500 V for auxiliary contacts conforming to VDE 0110
[Uimp] rated impulse withstand voltage	4 kV in enclosure
Mounting support	DIN rail
Connections - terminals	Auxiliary contact: connector 1 cable 2.5 mm ² - cable stiffness: flexible - with cable end Power circuit: connector 2 cable 16 mm ² - cable stiffness: flexible - without cable end Power circuit: connector 2 cable 4 mm ² - cable stiffness: flexible - with cable end Auxiliary contact: connector 2 cable 1.5 mm ² - cable stiffness: flexible - with cable end Power circuit: connector 1 cable 25 mm ² - cable stiffness: flexible - without cable end Power circuit: connector 1 cable 25 mm ² - cable stiffness: solid - without cable end Power circuit: connector 2 cable 6 mm ² - cable stiffness: solid - without cable end Auxiliary contact: connector 2 cable 1.5 mm ² - cable stiffness: solid - without cable end Auxiliary contact: connector 1 cable 2.5 mm ² - cable stiffness: flexible - without cable end Power circuit: connector 1 cable 16 mm ² - cable stiffness: flexible - with cable end Auxiliary contact: connector 2 cable 2.5 mm ² - cable stiffness: flexible - without cable end Auxiliary contact: connector 1 cable 1.5 mm ² - cable stiffness: solid - without cable end
Tightening torque	Auxiliary contact: 0.8 N.m - on connector - cable 2.5 mm ² Auxiliary contact: 0.8 N.m - on connector - cable 1.5 mm ² Power circuit: 3.5 N.m - on connector - cable 16 mm ² Power circuit: 3.5 N.m - on connector - cable 4 mm ² Power circuit: 3.5 N.m - on connector - cable 6 mm ² Power circuit: 3.5 N.m - on connector - cable 25 mm ²
[Ue] rated operational voltage	<= 250 V AC for auxiliary contacts <= 250 V AC 400 Hz for power circuit

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Irms rated making capacity	120 A at 400 V AC for power circuit conforming to IEC 61095
Permissible short-time rating	100 A (<= 40 °C) - short time current duration: 30 s - for power circuit 320 A (<= 40 °C) - short time current duration: 10 s - for power circuit
Average impedance	2 mOhm at 50 Hz - lth 40 A for power circuit
Power dissipation per pole	3.2 W AC-7A 3.2 W AC-7B
Inrush power in VA	34 VA at 20 °C
Hold-in power consumption in VA	4.6 VA at 20 °C 50 Hz
Operating time	10...25 ms opening 10...30 ms closing
Mechanical durability	1000000 cycles
Operating rate	300 cyc/h at <= 50 °C
Height	81 mm
Width	35 mm
Depth	65 mm
Product weight	0.23 kg

Environment

Standards	IEC 60947-5 IEC 61095 VDE 0637-3
Product certifications	NF
IP degree of protection	IP40 in enclosure conforming to VDE 0106 IP20 open state conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	<= 3000 m without derating in temperature
Fire resistance	850 °C conforming to IEC 60695-2-1
Shock resistance	10 gn contactor opened 15 gn contactor closed
Vibration resistance	3 gn 5...300 Hz contactor closed 2 gn 5...300 Hz contactor open
Heat dissipation	1.6 W at 50/60 Hz for control circuit