


CUSTOMER DATA SHEET	
CDS No: <b>64590</b>	Status: <b>On Sale</b>
Product: Jackson Safety* R30 FFP3 NR D Disposable Particulate Respirator with Comfort Straps and Dual Valve – Large Size	Date: <b>Jan 2011</b>
Countries sold into: EMEA	Version: <b>1</b>
	Replaces: <b>N/A</b>

FINISHED PRODUCT	
Property	Typical Values
Regulatory compliance	EN 149:2001 + A1 :2009
Nominal Protection Factor	50
Total Inward leakage (%)	Mean (N= 6) = 0.052% (Max allowed: 2%).
Inhalation Resistance at 95l/min	Mean (N=6) = 1.78 mbar (Max allowed: 3.0mbar)
Exhalation Resistance at 160 l/min	Mean (N=6) = 1.64 mbar (Max allowed: 3.0mbar)
Penetration: Solid Particles (NaCl 120mg)	Mean (N=12) = 0.069% (Max allowed: 1%)
Penetration: Liquid Particles (Parafin oil 120mg)	Mean (N=6) = 0.141% (Max allowed: 1%)
Exhalation Valve	Two, integrating clips for headband attachment
Product appearance	CE marks
	<p style="text-align: center;">KIMBERLY-CLARK <b>Jackson Safety*</b> www.kcprofessional.com 64590 FFP3 NR D EN149:2001 + A1:2009 <b>CE 0194</b></p>
Product weight:	35g
<b>Material Specification</b>	Supplier Specification KPSU-00666
1. Filter material	Three-layer mechanical and electrostatic filter media
2. Face seal	Full face seal: PVC foam + extra soft cloth.
3. Head straps	Comfort extra wide woven elastic – grey
4. Head band attachment	Attached to the valve-clip
5. Nose clip	Aluminium
6. Dual Valves	ABS red
7. All materials	Free of silicone and latex
<b>Colour Coded:</b>	Colour code: Red
<b>Additional features:</b>	Passed clogging test according to EN 149: 2001 (clause 7.17)
<b>Donning instructions:</b>	See: <a href="http://www.kc-safety.com/donvideo">www.kc-safety.com/donvideo</a>

PALLETISATION	
Unit of sale: 10 respirators/box, 8 boxes/case	Net weight/case 2.8Kg
Case size LxWxH: 56.8 x 26.0 x 39.1cm (OD)	Gross weight/case 3.6 Kg
Pallet Type	E5
Cases/pallet	18
Cases/layer	6
Layers/pallet	3

Features	Benefits
<ul style="list-style-type: none"> <li>Large size</li> <li>Comfort strap</li> <li>Dual exhalation valve</li> <li>Red colour coding</li> <li>Full face seal made of water repellent material and covered with soft cloth</li> <li>Adjustable head straps</li> <li>Tested at 120mg and passed clogging test</li> </ul>	<ul style="list-style-type: none"> <li>Increased face cover for a wider range of facial sizes.</li> <li>Provides improved use conditions to the wearer during the work shift</li> <li>Reduced breathing out resistance as exhaled air is better distributed</li> <li>Easy recognition of performance level (FFP3)</li> <li>Better sealing that reduces fogging on safety glasses with improved comfort when in contact with the facial skin</li> <li>Increase comfort and secure fit</li> <li>Increased capacity to operate longer in dusty environments</li> </ul>

NOTE
This data was generated from samples which were taken to be typical of standard product. The data is given for information only. Additional information can be supplied on request.

CONFIDENTIALITY STATEMENT
These specifications and the confidential information contained herein are the property of Kimberly-Clark. Copies of this material are the property of Kimberly-Clark and should be made only if absolutely necessary. Copies, like the originals, are considered as trade secrets.