

Datasheet

## RS Pro NPI43C Series Wire-wound SMD Inductor 10 $\mu$ H $\pm$ 20% Wire-Wound 1.1A Idc

RS Stock No: 740-9397



### Product Details

RS Pro wire-wound SMD inductor offers inductance of 10  $\mu$ H and withstands DC current up to 1.1 A. It works with DC-DC converters and DC-AC inverters. This compact filter is suitable for both flow and reflow soldering.

### Features and Benefits

- High current, small size (up to 4 amps)
- Surface mountable construction
- High inductance (up to 680  $\mu$ h)
- Suitable for use in DC/DC converters, DC/AC inverters
- Lead free compatible

**Specifications:**

Inductor Construction	Wire Wound
Shielded	No
Depth	4 mm
Dimensions	4.5 x 4 x 3.2 mm
Height	3.2 mm
Length	4.5 mm
Maximum DC Current	1.1 A
Maximum DC Resistance	190 mΩ
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Tolerance	±20%
Inductance	10 μH
Package/Case	43
Package Type	Tape & Reel