



4-1393800-6 Product Details



4-1393800-6

TE Part Number: 4-1393800-6

Active

Add to Part List

Communications/Signal PC Board Relays

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- V23008, V23009/Power Relay 15 Series
- DC Actuating System
- Input Voltage = 24 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 15 Amps.

[View all Features](#) | [Find Similar Products](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Termination Type = Solder/Plug-In Terminals

Electrical Characteristics:

- Actuating System = DC
- Input Voltage (VDC) = 24
- Contact Current Rating (Amps.) = 15
- [Coil Resistance \(Ω\)](#) = 300
- Coil Power, Nominal (mW) = 2000
- Dielectric Between Coil and Contacts (V rms) = 2500

Body Related Features:

- Series = V23008, V23009/Power Relay 15
- Polarized = No

Contact Related Features:

- Mounting Options = Socket
- Enclosure = Dust Protected
- [FCC Part 68 Isolation](#) = No
- Approved Standards = None
- Contact Material = Silver Nickel
- Approx. Dimensions (L x W x H) (mm [in]) = 53.00 x 46.50 x 61.00 [2.087 x 1.831 x 2.402]
- Compatible Socket = Without
- Contact Type = Single
- Pin Configuration = Industry Standard

Configuration Related Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- [Coil Magnetic System](#) = Non Polarized, Monostable
- Coil Suppression Diode = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Other:

- Brand = Axicom