

Plastic label - EMLP (27X27)R SR - 0827467

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Plastic label, Roll, silver, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X1.2, Mounting type: Adhesive, Lettering field: 27 x 27 mm

Why buy this product

- Quick and cost-effective labeling with THERMOMARK ... printers
- High level of resistance to chemical and mechanical influences
- The EMLP ... self-adhesive markers are equivalent to engraved labels
- High-quality appearance
- Primarily used for marking electrical components, devices, and buttons



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 430845
Weight per Piece (excluding packing)	318.0 g
Custom tariff number	39199000
Country of origin	Germany

Technical data

Dimensions

Length (b)	27 mm
Width (a)	27 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (assembly)	18 °C ... 40 °C

General

Color	silver
Components	free from silicone and halogen
Inflammability class according to UL 94	V0
Material	Polyester

Plastic label - EMLP (27X27)R SR - 0827467

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	500
Number of individual labels per row	2
RoHS compliant	Yes
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146257 THERMOMARK S1.1
	5146231 THERMOMARK X1.2
	5146477 THERMOMARK ROLL
	5145313 THERMOMARK S1
	5145274 THERMOMARK X1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
	0829544 THERMOMARK-RIBBON 110 BU
	0829542 THERMOMARK-RIBBON 110 GN
	0829543 THERMOMARK-RIBBON 110 RD
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Burning behaviour	self-extinguishing
Foil strength	175 µm
Adhesive strength	400 µm
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137

Plastic label - EMLP (27X27)R SR - 0827467

Classifications

eCl@ss

eCl@ss 7.0	27141137
------------	----------

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

Marker carriers

Marker carriers - CARRIER-EMP 22 (27X27) - 0827449



Marker carriers, black, unlabeled, Mounting type: Screws, rivets, Diameter: 22 mm, Lettering field: 27 x 27 mm

Marker carriers - CARRIER-EMLP 22 (27X27) - 0828988



Marker carriers, black, unlabeled, Mounting type: Screws, rivets, Diameter: 22 mm, Lettering field: 27 x 27 mm

