






-



YELLOW/GREEN BI-COLOR	2057134-2
RED/GREEN BI-COLOR	2057134-1
LED COLORS	PART NUMBER

*THIS DRAWING IS A CONSULTING DOCUMENT FOR THE CONSULTING ORGANIZATION IT IS SUBJECT TO THE REVIEW AND APPROVAL OF THE CONSULTING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISIONS.		OWN M. SHIRK 08APR2008 CHK P. HENRY 08APR2008 APP'D P. HENRY 08APR2008		 Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: (mm)		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P L C ±.025 1 P L C ±.025 2 P L C ±.025 3 P L C ±.025 4 P L C ±.025 ANGLES ±2°		NAME RECEPTACLE ASSEMBLY, 2X12, NON MAGNETICS, RJ POINT FIVE -	
		PRODUCT SPEC APPLICATION SPEC		SIZE CAGE CODE DRAWING NO - - -	
MATERIAL -		FINISH -		RESTRICTED TO A 00779 C-2057134	
WEIGHT -		CUSTOMER DRAWING		SCALE 1 3 4 SHEET 1 OF 5 REV A	


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AG	00	-	-	SEE SHEET 1	-	-






RECOMMENDED PCB LAYOUT
SCALE 5:1


THIS DRAWING, ITS CONTENTS, SCHEMATIC, AND ALL INFORMATION CONTAINED HEREIN ARE UNCLASSIFIED EXCEPT WHERE SHOWN OTHERWISE BY CONTRACT FOR THE U.S. GOVERNMENT OR BY OTHER AUTHORITY.		DWN M. SHIRK 08APR2008	Tyco Electronics Harrisburg, PA 17105-3608	
CHK R. HENRY 08APR2008		APVD R. HENRY 08APR2008	NAME RECEPTACLE ASSEMBLY, 2X12, NON MAGNETICS, RJ POINT FIVE	
PRODUCT SPEC		APPLICATION SPEC		SIZE A
MATERIAL		WEIGHT		RESTRICTED TO
FINISH		SCALE 3:1		SHEET 2
CUSTOMER DRAWING		REV A		

LOC		DIST		REVISONS				DATE	DWN	APVD
P	LTR			DESCRIPTION						
				SEE SHEET 1						





RECOMMENDED PANEL CUTOUT





TYCO ELECTRONICS CORPORATION 1111 B. ROAD, SUITE 100, HARRISBURG, PA 17105-3608 SHOWN BY CONTACT FOR THE LATEST REVISION. NO MODIFICATION				DWN M. SHIRK 08APR2008	Tyco Electronics Harrisburg, PA 17105-3608			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK R. HENRY 08APR2008	APVD R. HENRY 08APR2008	NAME RECEPTACLE ASSEMBLY, 2X12, NON MAGNETICS, RJ POINT FIVE		
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC APPLICATION SPEC		SIZE CAGE CODE DRAWING NO		
MATERIAL		FINISH		WEIGHT		RESTRICTED TO		
-		-		-		A 00779 C-2057134		
CUSTOMER DRAWING				SCALE		SHEET		
				3:1		3 OF 5		
						REV A		

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	-	SEE SHEET 1	-	-	-	




TOP PORT



BOTTOM PORT

THIS DRAWING, IT'S CONTENTS, DESIGN AND ALL RIGHTS RESERVED BY TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. FOR THE LATEST INFORMATION, CONTACT YOUR LOCAL TYCO REPRESENTATIVE.		DWN M. SHIRK 08APR2008	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK R. HENRY 08APR2008	NAME RECEPTACLE ASSEMBLY, 2X12, NON MAGNETICS, RJ POINT FIVE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±°		APVD R. HENRY 08APR2008	PRODUCT SPEC APPLICATION SPEC	
MATERIAL :		FINISH :	WEIGHT -	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 3:1	SHEET 4	REV A



RECOMMENDED HOLE DIMENSIONS FOR SHIELD PINS

THICKNESS	PLATING
0.004-0.010	HOT AIR SOLDER LEVELING (HASL) TIN-LEAD (Sn Pb)
0.0005-0.001	IMMERSION TIN (Sn)
0.0002-0.0005	ORGANIC SOLDERABILITY PRESERVATIVE (OSP)
0.0001-0.0005 Au, 0.004-0.0076 Ni	IMMERSION GOLD (Au) OVER NICKEL (Ni) (ENIG)
0.010-0.025	TIN LEAD PLATING (Sn Pb)
0.0001-0.00015	IMMERSION SILVER (Ag)