


PART No MATRIX



Specification.

(See alternative variations in matrix key)
 Insert Material - PUR (30% Glass Filled)
 Contact Material - Brass (CuZn36)
 Contact Plating - 2um Ni, 0.70um Gold
 Coupling Nuts - Nickel Plated Brass
 Seal - Viton O-Ring
 Protection Class - IP68
 Voltage Rating - 30 VAC / 36 VDC
 Contact Current Rating - 4 Amps
 Overmoulding - PUR

OPTIONS

Coupling Nut Material
 Blank=Standard
 1=Stainless Steel
 5=Delrin

ECN	Rev	By	Descriptions	Date	Approved
N/A	A	GC	First Issue	13.05.04	NW



This drawing and its contents are the proprietary and confidential property of Woodhead Industries Inc. and/or its subsidiaries and may not be used or disclosed to others without the express prior written consent of Woodhead Industries Inc. and/or its subsidiaries.

NAME	DATE
Drawn G.GREEN	13.05.04
Checked N.WITTS	13.05.04
Approved N.WITTS	13.05.04

Material: SEE SPECIFICATION
 Finish: SEE SPECIFICATION
 Dimensions in MM:
 0.0 ± 0.25mm
 0.00 ± 0.10mm
 0.000 ± 0.025mm
 Angles ± 1°

Part No. **808007P02MXXX** Size **A4**
 Description
MICRO CHANGE 80 SERIES JUMPER CONNECTOR LEAD

Drawing No. **808007P02MXXX** Rev **A**
 Scale **NTS** SHEET **1 OF 1**

Plate #:	8	7	6	5	4	3	2	1
----------	---	---	---	---	---	---	---	---