



Main

Range of product	Acti 9
Modular device name	IHP +
Device short name	IHP + 2c
Product or component type	Programmable digital time switch
Product compatibility	Mechanical compatibility with electrical distribution comb busbars
Number of channels	2
Battery type	Lithium
Function available	Automatic time changeover Pulse programming
Type of setting	Absence for holidays function Random function
Provided equipment	Memory key
Language	Danish Dutch English Finnish French Norwegian Swedish

Complementary

Device application	Building
Measurement accuracy	+/- 1 s/day
Cycle duration	24 hours + 7 days
Maximum number of switchings	84
Minimum interval duration	1 s
Measurement accuracy	+/- 1 s/day 20 °C
Number of inputs	2 with a switch or a pushbutton
Power consumption	7 VA
Maximum switching current	16 A - 250 V AC pf = 1 10 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V (+/- 10 %) AC 50/60 Hz
Display type	Backlit LCD
Battery life	6 yr
Backup time	6 years time and program saving
Product mounting	DIN rail
9 mm pitches	5
Colour tint	White(RAL 9003)
Width	45 mm
Height	85 mm
Depth	66 mm

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP20 B

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0946 - Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - go to CaP for more details
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Available Download End Of Life Manual

Contractual warranty

Period	18 months
--------	-----------