

## Plastic label with drill hole - EMLP 24 (30X12)R - 0819550

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Plastic label with drill hole, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 30 x 12 mm




The figure shows the white version

### Why buy this product

- Quick and cost-effective labeling with THERMOMARK ... printers
- The EMLP 24 ... self-adhesive markers are ideal for marking electrical buttons
- Labeling service: Phoenix Contact can custom-label all EMLP ... markers according to your requirements
- High-quality appearance
- High level of resistance to chemical and mechanical influences

### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 160681
Weight per Piece (excluding packing)	346.1 g
Custom tariff number	39199000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	40 mm
Width (a)	30 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (assembly)	18 °C ... 40 °C

#### General

Color	white
Components	free from silicone and halogen
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	500

# Plastic label with drill hole - EMLP 24 (30X12)R - 0819550

## Technical data

### General

Number of individual labels per row	2
RoHS compliant	Yes
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146257 THERMOMARK S1.1
	5146231 THERMOMARK X1.2
	5146477 THERMOMARK ROLL
	5145313 THERMOMARK S1
	5145274 THERMOMARK X1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
	0829544 THERMOMARK-RIBBON 110 BU
	0829542 THERMOMARK-RIBBON 110 GN
	0829543 THERMOMARK-RIBBON 110 RD
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Burning behaviour	self-extinguishing
Foil strength	175 µm
Adhesive strength	400 µm

## Classifications

### eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

## Plastic label with drill hole - EMLP 24 (30X12)R - 0819550

### Classifications

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410