




WIRING DIAGRAM					LOCKNUT LN-SS08					SPECIFICATIONS																																																								
										<table><tr><td>RATED OPERATING DISTANCE</td><td>2.0 mm = .079"</td></tr><tr><td>MOUNTING MODE</td><td>FLUSH</td></tr><tr><td>MIN. REPEAT ACCURACY</td><td>≤ 2%</td></tr><tr><td>TEMPERATURE DRIFT</td><td>≤ ± 10%</td></tr><tr><td>HYSTERESIS</td><td>3-15%</td></tr><tr><td>OPERATING TEMPERATURE</td><td>-25°C to +70°C (-13°F to +158°F)</td></tr><tr><td>RATED OPERATIONAL VOLTAGE</td><td>10-30 VDC</td></tr><tr><td>RESIDUAL RIPPLE</td><td>≤10%</td></tr><tr><td>RATED OPERATIONAL CURRENT (DC)</td><td>≤150 mA</td></tr><tr><td>NO-LOAD CURRENT</td><td>≤ 15 mA</td></tr><tr><td>RESIDUAL CURRENT</td><td>≤ 0.1 mA</td></tr><tr><td>RATED INSULATION VOLTAGE</td><td>≤ 0.5 kV</td></tr><tr><td>SHORT-CIRCUIT PROTECTED</td><td>YES</td></tr><tr><td>MAX VOLTAGE DROP</td><td>≤ 1.8 V</td></tr><tr><td>WIRE BREAKAGE PROTECTION</td><td>INCORPORATED</td></tr><tr><td>REVERSE POLARITY PROTECTION</td><td>INCORPORATED</td></tr><tr><td>OUTPUT FUNCTION</td><td>4-WIRE, CHANGE OVER, PNP</td></tr><tr><td>MAX. SWITCHING FREQUENCY</td><td>≤ 3.0 kHz</td></tr><tr><td>HOUSING MATERIAL</td><td>METAL, A4 1.4404 (AISI 316L)</td></tr><tr><td>ACTIVE FACE MATERIAL</td><td>PLASTIC, PA12-GF20</td></tr><tr><td>END CAP MATERIAL</td><td>PLASTIC, PP</td></tr><tr><td>CABLE</td><td>ø4.0, TPU</td></tr><tr><td>SHOCK RESISTANCE</td><td>30 g, 11 ms</td></tr><tr><td>VIBRATION RESISTANCE</td><td>55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)</td></tr><tr><td>DEGREE OF PROTECTION</td><td>IP67</td></tr><tr><td>SWITCHING STATUS INDICATION</td><td>LED: YELLOW</td></tr></table>					RATED OPERATING DISTANCE	2.0 mm = .079"	MOUNTING MODE	FLUSH	MIN. REPEAT ACCURACY	≤ 2%	TEMPERATURE DRIFT	≤ ± 10%	HYSTERESIS	3-15%	OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)	RATED OPERATIONAL VOLTAGE	10-30 VDC	RESIDUAL RIPPLE	≤10%	RATED OPERATIONAL CURRENT (DC)	≤150 mA	NO-LOAD CURRENT	≤ 15 mA	RESIDUAL CURRENT	≤ 0.1 mA	RATED INSULATION VOLTAGE	≤ 0.5 kV	SHORT-CIRCUIT PROTECTED	YES	MAX VOLTAGE DROP	≤ 1.8 V	WIRE BREAKAGE PROTECTION	INCORPORATED	REVERSE POLARITY PROTECTION	INCORPORATED	OUTPUT FUNCTION	4-WIRE, CHANGE OVER, PNP	MAX. SWITCHING FREQUENCY	≤ 3.0 kHz	HOUSING MATERIAL	METAL, A4 1.4404 (AISI 316L)	ACTIVE FACE MATERIAL	PLASTIC, PA12-GF20	END CAP MATERIAL	PLASTIC, PP	CABLE	ø4.0, TPU	SHOCK RESISTANCE	30 g, 11 ms	VIBRATION RESISTANCE	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)	DEGREE OF PROTECTION	IP67	SWITCHING STATUS INDICATION	LED: YELLOW
RATED OPERATING DISTANCE	2.0 mm = .079"																																																																	
MOUNTING MODE	FLUSH																																																																	
MIN. REPEAT ACCURACY	≤ 2%																																																																	
TEMPERATURE DRIFT	≤ ± 10%																																																																	
HYSTERESIS	3-15%																																																																	
OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)																																																																	
RATED OPERATIONAL VOLTAGE	10-30 VDC																																																																	
RESIDUAL RIPPLE	≤10%																																																																	
RATED OPERATIONAL CURRENT (DC)	≤150 mA																																																																	
NO-LOAD CURRENT	≤ 15 mA																																																																	
RESIDUAL CURRENT	≤ 0.1 mA																																																																	
RATED INSULATION VOLTAGE	≤ 0.5 kV																																																																	
SHORT-CIRCUIT PROTECTED	YES																																																																	
MAX VOLTAGE DROP	≤ 1.8 V																																																																	
WIRE BREAKAGE PROTECTION	INCORPORATED																																																																	
REVERSE POLARITY PROTECTION	INCORPORATED																																																																	
OUTPUT FUNCTION	4-WIRE, CHANGE OVER, PNP																																																																	
MAX. SWITCHING FREQUENCY	≤ 3.0 kHz																																																																	
HOUSING MATERIAL	METAL, A4 1.4404 (AISI 316L)																																																																	
ACTIVE FACE MATERIAL	PLASTIC, PA12-GF20																																																																	
END CAP MATERIAL	PLASTIC, PP																																																																	
CABLE	ø4.0, TPU																																																																	
SHOCK RESISTANCE	30 g, 11 ms																																																																	
VIBRATION RESISTANCE	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)																																																																	
DEGREE OF PROTECTION	IP67																																																																	
SWITCHING STATUS INDICATION	LED: YELLOW																																																																	
																																																																		
SOURCE DRAWING - FOR REFERENCE ONLY																																																																		
<table><tr><td colspan="5">RELATED DOCUMENTS</td></tr><tr><td>1.</td><td></td><td></td><td></td><td></td></tr><tr><td>2.</td><td></td><td></td><td></td><td></td></tr><tr><td>3.</td><td></td><td></td><td></td><td></td></tr><tr><td>4.</td><td></td><td></td><td></td><td></td></tr></table>					RELATED DOCUMENTS					1.					2.					3.					4.					<table><tr><td colspan="2">3RD ANGLE PROJECTION</td></tr><tr><td></td><td></td></tr></table>		3RD ANGLE PROJECTION				<table><tr><td colspan="2">THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</td></tr><tr><td>DRFT</td><td>RWC</td></tr><tr><td>DATE</td><td>01/21/10</td></tr><tr><td>DSGN</td><td>SCALE 1=1.0</td></tr></table>		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		DRFT	RWC	DATE	01/21/10	DSGN	SCALE 1=1.0	<table><tr><td colspan="3">TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</td></tr><tr><td colspan="3">DESCRIPTION</td></tr><tr><td colspan="3">BI 2-EG08-VP6X-0.2M-RS 4.4T</td></tr></table>			TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com			DESCRIPTION			BI 2-EG08-VP6X-0.2M-RS 4.4T											
RELATED DOCUMENTS																																																																		
1.																																																																		
2.																																																																		
3.																																																																		
4.																																																																		
3RD ANGLE PROJECTION																																																																		
THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.																																																																		
DRFT	RWC																																																																	
DATE	01/21/10																																																																	
DSGN	SCALE 1=1.0																																																																	
TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com																																																																		
DESCRIPTION																																																																		
BI 2-EG08-VP6X-0.2M-RS 4.4T																																																																		
<table><tr><td colspan="5">MATERIAL</td></tr><tr><td colspan="5">SEE SPECS</td></tr></table>					MATERIAL					SEE SPECS					<table><tr><td colspan="2">ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</td></tr><tr><td colspan="2">CONTACT TURCK FOR MORE INFORMATION</td></tr></table>		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		CONTACT TURCK FOR MORE INFORMATION		<table><tr><td colspan="3">UNIT OF MEASUREMENT</td></tr><tr><td colspan="3">INCH [MILLIMETER]</td></tr><tr><td colspan="3">DO NOT SCALE THIS DRAWING</td></tr></table>			UNIT OF MEASUREMENT			INCH [MILLIMETER]			DO NOT SCALE THIS DRAWING			<table><tr><td colspan="2">IDENTIFICATION NO.</td></tr><tr><td colspan="2">S1604680</td></tr><tr><td colspan="2">REV</td></tr><tr><td colspan="2">C</td></tr></table>		IDENTIFICATION NO.		S1604680		REV		C																									
MATERIAL																																																																		
SEE SPECS																																																																		
ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY																																																																		
CONTACT TURCK FOR MORE INFORMATION																																																																		
UNIT OF MEASUREMENT																																																																		
INCH [MILLIMETER]																																																																		
DO NOT SCALE THIS DRAWING																																																																		
IDENTIFICATION NO.																																																																		
S1604680																																																																		
REV																																																																		
C																																																																		
C	DRAWING PROCESSED AS PART OF ECO 33971				CBM	04/06/11	33971																																																											
REV	DESCRIPTION				BY	DATE	ECO NO.																																																											
							FILE: S1604680		SHEET 1 OF 1																																																									