



ACCESSORIES 6.3 (1/4")

2030

CONVERTOR 1/4" TO 3/8"

- Acc. to DIN 3123, ISO 3316
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

6.3
1/4"
10
3/8"



Code	No.	□"	□	■"	■	↳mm↳	↳	↳	£
6170080	2030	1/4	6.3	3/8	10	26	20	10	

2087

SLIDING T BAR 1/4"

- Acc. to DIN 3122, ISO 3315
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

6.3
1/4"



Code	No.	■"	■	↳mm↳	↳	↳	£
6170160	2087	1/4	6.3	115	39	5	

2087 A

SLIDING T BAR WITH RELEASE 1/4"

- Secured against unintentional removal
- GEDORE vanadium steel 31CrV3, polished, chrome-plated
- Turn handle for easy locking and releasing
- Accidental release when working is prevented because of the asymmetrical release point
- Particularly useful for work in sensitive areas where certainty against loss is a theme
- Examples: Aircraft engine, work in deep machine bodies
- DBGM (German utility patent)

6.3
1/4"



Code	No.	■"	■	↳mm↳	↳	↳	£
1834398	2087 A	1/4	6.3	115	48	1	

2088

FLEXIBLE EXTENSION 1/4"

- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

6.3
1/4"



Code	No.	■"	■	↳mm↳	↳	↳	£
6170240	2088	1/4	6.3	120	46	10	

2090

EXTENSION 1/4"

- Acc. to DIN 3123, ISO 3316
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, polished, chrome-plated
- * not standardised

6.3
1/4"



Code	No.	*	■"	■	↳mm↳	↳	↳	£
6170320	2090-2		1/4	6.3	55	25	10	
6170400	2090-4		1/4	6.3	97	41	10	
6171210	2090-6		1/4	6.3	148	61	10	
6173340	2090-12	*	1/4	6.3	305	124	10	

2090 A

EXTENSION 1/4" with release

- Easy access to deep-fitting screws in confined areas
- No unintentional release of the socket from the extension due to safety ring
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, ball locking device

6.3
1/4"




Code	No.	■"	■	↳mm↳	↳	↳	£
1932284	2090 A-2	1/4	6.3	55	30	1	
1932292	2090 A-4	1/4	6.3	97	50	1	
1932306	2090 A-12	1/4	6.3	305	125	1	

2090 KR

UNIVERSAL EXTENSION 1/4"

- With ball end
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- The extension is able to pivot up to 15°
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

6.3
1/4"



Code	No.	■"	■	↳mm↳	↳	↳	£
1812564	2090 KR-2	1/4	6.3	55	24	1	
1812572	2090 KR-4	1/4	6.3	97	45	1	
6121030	2090 KR-6	1/4	6.3	148	60	10	

2094

COUPLER 1/4"

- Acc. to DIN 3122, ISO 3315
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

6.3
1/4"



Code	No.	■"	■	↳mm↳	↳	↳	£
6170830	2094	1/4	6.3	19.8	6	10	

2095

UNIVERSAL JOINT 1/4"

- Acc. to DIN 3123, ISO 3316
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

6.3
1/4"

Code	No.	□"	■	□"	□	↳mm↳	↻	📦	£
6170910	2095	1/4	6.3	1/4	6.3	38	26	10	

2097

SWIVEL HANDLE 1/4"

- Acc. to DIN 3122, ISO 3315
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, polished, chrome-plated, square drive manganese-phosphated

6.3
1/4"

Code	No.	□"	■	↳mm↳	↻	📦	£
6171050	2097	1/4	6.3	146	94	10	

2098

DRIVING HANDLE 1/4"

- Acc. to DIN 3122, ISO 3315
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device

6.3
1/4"

Code	No.	□"	■	↳mm↳	↻	📦	£
6171480	2098	1/4	6.3	140	70	10	

2098 K

DRIVING HANDLE 1/4" short pattern

- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device

6.3
1/4"

Code	No.	□"	■	↳mm↳	↻	📦	£
1953788	2098 K	1/4	6.3	70	34	1	

2098 T

DRIVING HANDLE 1/4"

- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- With bit adaptor no. 620 also suitable for 1/4" bits
- Easy access to deep-fitting screws in confined areas
- The danger of the tool canting, is reduced by the central positioning of the square drive
- With hanging hole
- GEDORE vanadium steel 31CrV3, chrome-plated

6.3
1/4"

Code	No.	□"	■	↳mm↳	↻	📦	£
1939998	2098 T	1/4	6.3	300	150	1	

2099

TELESCOPIC EXTENSION 1/4" magnetic

- With 1/4" female square drive and 1/4" female hexagon drive
- Automatic, form-fit connection
- Adjustable in 10 mm steps from 186-296 mm
- Suitable for 1/4" bits as well as with adaptor no. 673 for sockets up to 13 mm
- Made of quality steel, manganese-phosphated resp. chrome-plated

6.3
1/4"
6.3
1/4"
🔒

Code	No.	□"	□	○"	○	↳mm↳	↻	📦	£
1888455	2099	1/4	6.3	1/4	6.3	186-296	205	1	

SL 2013

TOOL HOLDING RAIL, MAGNETIC 1/4" empty

- External squares to take 13 standard commercial 6.3 mm (1/4") sockets
- Two female square adaptors to take ratchets, sliding T bars, extensions etc.
- A strong magnet securely holds the socket rail to ferrous metals
- Additional holes are provided for wall mounting the socket rail or attaching to non-ferrous materials
- The sockets are securely locked by the ball at the square-drive end by turning them 90°
- It is a simple matter to "unlock" and remove the sockets, by turning them 90° in the opposing direction
- Delivery without tools

6.3
1/4"
6.3
1/4"
🔒

Code	No.	↳mm↳	mm	↳mm↳	📦	£
1761080	SL 2013	380	33	355	1	

S 2032-05

ADAPTOR SET 1/4" 5 pieces

- Set of reducers and converters 1/4" - 3/4"
- Reducers 1930, 3020
- Convertors 2030, 3019, 1932
- In transparent plastic box, dimensions: L 134 x W 51 x H 51 mm, foam insert light-blue
- Please take note of the maximum capacity of the external squares of the reducers acc. to DIN 3123, ISO 3316

6.3
1/4"
10
3/8
12.5
1/2
20
3/4

Code	No.	Contents	↻	📦	£
1729071	S 2032-05	2030 3020 3019 1930 1932	340	1	