

Data sheet

Commercial Art.No.: 57.510.0555.0

Feed-through terminal WKN 10 SF

Feed-through terminal with Screw connection for mounting on TS 35/ TS 32, nominal cross section: 10 mm², Width: 10 mm, Color: grey



| | |
|--------------------|---------------|
| Commercial Art.No. | 57.510.0555.0 |
| EAN | 4049088149115 |
| Order Unit | 50 |

Certificates / Approvals

Technical data

General

| | |
|--|--------------------------------|
| Nominal cross section | 10 mm ² |
| Colour | Grey |
| Number of levels | 1 |
| Number of clamp positions per level | 2 |
| Width/grid dimension | 10 mm |
| Insulating housing | PA666 |
| Inflammability class of insulation material acc. with UL94 | V0 |
| Explosion-tested version "Ex e" | No |
| Mounting method | DIN rail (top hat rail)/G-rail |
| Terminal blocks for electrical installations | No |

Technical data

| | |
|-----------------------------|---------------|
| Rated current | 57 A |
| Rated voltage | 800 V |
| Rated impulse voltage | 8 kV |
| Pollution degree | 3 |
| Closing plate required | Yes |
| Type of insulation material | Thermoplastic |
| Length | 55 mm |

Connection Data

| | |
|-------------------------------------|---------------------|
| Connection type 1 | Screw connection |
| Connection type 2 | Screw connection |
| Minimum cross section solid | 1.5 mm ² |
| Maximum cross section solid | 16 mm ² |
| Minimum cross section fine stranded | 2.5 mm ² |
| Maximum cross section fine stranded | 10 mm ² |
| Minimum cross section stranded | 10 mm ² |
| Maximum cross section stranded | 16 mm ² |

| | |
|---------------------------|-------|
| Wire strip length | 13 mm |
| Torque conductor mounting | 2 Nm |

Classification

| | |
|----------|----------|
| ETIM 7.0 | EC000897 |
| ETIM 6.0 | EC000897 |

Accessories

| Commercial Art.No.: | Article-type description: | Description: |
|---------------------|---------------------------|--------------|
|---------------------|---------------------------|--------------|

Fits with

| Commercial Art.No.: | Article-type description: | Description: |
|---------------------|---------------------------|--------------|
|---------------------|---------------------------|--------------|