

## Surge protection plug - TT-UKK5-T-V-24DC-ST - 2788391

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective plug with varistor for TERMITRAB base element TT-UKK5-T-BE, nominal voltage: 24 V DC

### Why buy this product

- Can be used in the signal circuits of electronic controllers



### Key commercial data

Packing unit	50 pc
GTIN	 4 017918 071516
Weight per Piece (excluding packing)	8.1 g
Custom tariff number	85363030
Country of origin	Greece

### Technical data

#### Dimensions

Height	52 mm
Width	6.2 mm
Length	41.5 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Degree of protection	IP20

#### General

Housing material	PA
Inflammability class according to UL 94	V2
Color	black
Standards for air and creepage distances	VDE 0110-1
Mounting type	On base element
Type	Single-level terminal block

# Surge protection plug - TT-UKK5-T-V-24DC-ST - 2788391

## Technical data

### General

Number of positions	1
Direction of action	Line-Line

### Protective circuit

IEC test classification	C1
	C3
VDE requirement class	C1
	C3
Nominal voltage $U_N$	24 V DC
Maximum continuous operating voltage $U_C$	31 V DC
	25 V AC
Maximum continuous voltage $U_C$ (wire-wire)	31 V DC
Maximum continuous voltage $U_C$ (wire-ground)	25 V DC
Nominal current $I_N$	26 A (40°C)
Operating effective current $I_C$ at $U_C$	$\leq 150 \mu A$
Nominal discharge current $I_n$ (8/20) $\mu s$ (Core-Core)	350 A
Total surge current (8/20) $\mu s$	350 A
Max. discharge current $I_{max}$ (8/20) $\mu s$ maximum (Core-Core)	1 kA
Nominal pulse current $I_{an}$ (10/1000) $\mu s$ (Core-Core)	25 A
Residual voltage at $I_n$ , (conductor-conductor)	$\leq 130 V$
Response time $t_A$ (Core-Core)	$\leq 25 ns$
Capacity (Core-Core)	typ. 4.6 nF
Impulse durability (conductor-conductor)	C1 - 500 V / 250 A
	C3 - 10 A

### Connection data

Connection method	Screw connection (in connection with the base element)
Connection type IN	TERMITRAB plug-in system
Connection type OUT	TERMITRAB plug-in system
Screw thread	M3
Tightening torque	0.5 Nm
Stripping length	8 mm
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	4 mm <sup>2</sup>
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

### Standards and Regulations

Standards/regulations	IEC 61643-21
-----------------------	--------------

# Surge protection plug - TT-UKK5-T-V-24DC-ST - 2788391

## Classifications

### eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

### ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943

### UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

## Accessories

### Accessories

# Surge protection plug - TT-UKK5-T-V-24DC-ST - 2788391

## Accessories

### End cover

End cover - D-TERMITRAB-UK 5 - 2794990



Cover for setting the end of a TT-UK 5 row of terminal blocks, color: black

---

### Labeled terminal marker

Zack Marker strip, flat - ZBF 6,LGS:FORTL.ZAHLEN - 0808749



Zack Marker strip, flat, Strip, white, labeled, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - 100, Mounting type: Snap into flat marker groove, for terminal block width: 6.2 mm, Lettering field: 5.15 x 6.15 mm

---

Marker for terminal blocks - ZB 6,LGS:L1-N,PE - 1051414



Marker for terminal blocks, Strip, white, labeled, can be labeled with: Plotter, Horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

---

Marker for terminal blocks - ZB 6,LGS:U-N - 1051430



Marker for terminal blocks, Strip, white, labeled, can be labeled with: Plotter, Printed horizontally: U, V, W, N, GND, U, V, W, N, GND, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

---

Zack marker strip - ZB 6,LGS:FORTL.ZAHLEN - 1051016



Zack marker strip, Strip, white, labeled, can be labeled with: Plotter, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

---

### Marker pen

## Surge protection plug - TT-UKK5-T-V-24DC-ST - 2788391

### Accessories

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

---

### Terminal marking

Zack Marker strip, flat - ZBF 6:UNBEDRUCKT - 0808710



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into flat marker groove, for terminal block width: 6.2 mm, Lettering field: 5.15 x 6.15 mm

---

Zack Marker strip, flat - ZBF 6/WH-100:UNBEDRUCKT - 0808736



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into flat marker groove, for terminal block width: 6.2 mm, Lettering field: 5.15 x 6.15 mm

---

Zack marker strip - ZB 6:UNBEDRUCKT - 1051003



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

---

### Necessary add-on products

Surge protection base element - TT-UKK5-T-BE - 2788401



TERMITRAB base element with universal foot, with screw connections on both sides.

---

### Additional products

# Surge protection plug - TT-UKK5-T-V-24DC-ST - 2788391

## Accessories

Shield connection - SSA 3-6 - 2839295



shield fast connections for conductor diameter 3 - 6 mm. Potential connection cable: 200 mm, black

Shield connection - SSA 5-10 - 2839512



Shield fast connection for conductor diameters 5 - 10 mm. Potential connection cable: 200 mm, black

## Drawings

Circuit diagram

