


	LOC	DIST	REVISIONS					
	—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
NUMMER	827	730		1	ZEICHNUNG NEU ERSTELLT	31.08.89	—	WRULICH
VERWENDET FÜR				2	REVISED PER ECO-09-023313	12OCT09	—	AEG
WAR NR.	—			3	ECR-10-025774	28JAN11	KK	HMR

POLZ	L±0.3	BESTELL-NR.
—	—	—
2	5.08	827 730 2
3	7.62	3
4	10.16	4
5	12.70	5
6	15.24	6
7	17.78	7
8	20.32	8
9	22.86	9
10	25.40	10
11	27.94	11
12	30.48	12
13	33.02	13
14	35.56	14
15	38.10	15
16	40.64	16
17	43.18	17
18	45.72	18
19	48.26	19
20	50.80	20
21	53.34	21
22	55.88	22
23	58.42	23
24	60.96	24
25	63.50	25
26	66.04	26
27	68.58	27
28	71.12	28
29	73.66	29
30	76.20	30
31	78.74	31
32	81.28	32
33	83.82	33
34	86.36	34
35	88.90	35
36	91.44	36
37	93.98	37
38	96.52	38
39	99.06	39
40	101.60	40
41	104.14	41
42	106.68	42
43	109.22	43
44	111.76	44
45	114.30	45
46	116.84	46
47	119.38	47
48	121.92	48
49	124.46	49
50	127.00	50



① STECKSEITE: IM BEREICH "F" 0.8 μm GOLD ÜBER 1.27 μm NICKEL
LÖTSEITE: MIN. 2.0 μm ZINN ÜBER 1.27 μm NICKEL

② OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

③ OBSOLETE

CAD-ORIGINAL
ZEICHNUNG NICHT ÄNDERN

KONTAKTSTIFT	Cu Sn	①
STIFTGEHÄUSE	PBTP-GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

ZEICHNUNG GÜLTIG AB 35/89...

DIMENSIONS:		DWN	31.08.89		MATERIAL	—		FINISH	—	
mm		CHK	—		TE Connectivity					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	—							
±0.2 mm		PRODUCT SPEC	—		NAME AMPMODU II STIFTLISTE SONDERAUSFUEHRUNG					
0 PLC ± —		APPLICATION SPEC	—							
1 PLC ± —		—	—		SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO
2 PLC ± —		—	—		A4	00779	C-827730			—
3 PLC ± —		WEIGHT	—		SCALE 4:1 SHEET 1 OF 1 REV 3					
4 PLC ± —		—	—							
ANGLES ± —		CUSTOMER DRAWING								
