

Accuratus AccuMed 540 v2 VESA - Sealed Clinical Computer Keyboard

USB Mini Sealed IP67 Antibacterial Medical Keypad with Hi Res Touchpad and VESA mounting

Keyboard model no. KYBNA-540VESA-W

About

The AccuMed 540 VESA keyboard offers VESA mounting, perfect for keyboard arms, vehicle mounting or any other fixing. The AccuMed 540 also offers ultra slim keys whilst still offering an excellent tactile and responsive feel. The keyboard can be fully cleaned and wiped over in literally seconds and also has a handy power on/off button, enabling you to turn the keyboard off during cleaning, preventing keys sending messages to the PC. There is also a cleaning reminder which enables you to set the time span required for cleaning (30min, 1hr, 2hr or 4hr) which aids infection control as the user is prompted to clean this washable keyboard regularly. The 540 has our NANOARMOUR-2 dual layer antibacterial protection impregnated in the silicone and coated on the surface to aid in deactivating germs/build up of bacteria & virus's.

What is NANOARMOUR and how does it work?

NANOARMOUR contains silver nano particles which have an antibacterial activity. Silver nano particles have been used on a wide range of high-end medical products and have been proven to help deactivate Escherichia coli, Staphylococcus aureus and so many more bacteria... The NANOARMOUR properties will help to deactivate bacteria and virus's. Please contact us if you would like a test report on the technology used.

As the silver nano particles size is about 1-20 nm while the bacteria cell size is 100-1000 nm, silver nano particles can enter into the cell then release the silver ion to combine with thiol, carboxyl, hydroxyl group in cell to deactivate the following functions:

- 1 - Combine with respiratory enzyme to cause suffocation
- 2 - Bind with protease enzyme and cause indigestion
- 3 - Bind with DNA's and inhibit cell replication

After the bacterial cell functions are disturbed by the silver nano particles, cell damage and the death of the bacteria cell occur, also inhibiting cell reproduction.

Specification

- USB interface
- Available in black or white, other colours made on request
- Mini UK key layout with clear and easy to read key legends
- VESA mount pattern on the rear of the keyboard (75mm x 75mm), brass screws and washers are provided. VESA Standard MIS-D 75mm, M4 threads 7mm deep.
- High resolution large area wide touchpad with left / right mouse buttons and scrolling
- Carbon on gold high quality key contact technology
- New design ultra slim 1mm tall keys so that the keyboard can be easily wiped clean
- Keys still have a tactile feel to allow for comfortable and natural typing

- Illuminated cleaning reminder, enabling time span to be set for cleaning (30min, 1hr, 2hr or 4 hr)
- Power on/off button so the keyboard can be turned off during cleaning, preventing key strokes being sent to the computer
- Moulded USB plug cover to put over the USB plug, so the keyboard can be immersed and cleaned away from the computer
- Durable rigid silicone body with NANOARMOUR-2 dual layer antibacterial protection impregnated into the silicone and coated on the surface to aid with deactivating a widespread spectrum of bacteria, virus, fungi and algae.
- The NANOARMOUR technology is made up using Silver nano particles
- Passes the JIS Z 2801:2001 antimicrobial test standards
- Designed so that there are no areas around keys that dirt and germs can collect
- Easy to clean with a wipe, wet cloth or in water
- Rigid keyboard with sealed silicone coating
- Fully sealed silicone casing, dust, water and chemical resistant, IP67 rated
- Designed to work in temperatures from -20'C to +50'C
- Status LED's (Caps, Num & Scroll Lock)
- White box environment friendly packaging

Physical Specification

- Dimensions: 289 x 227 x 19mm (l x w x h)
- Weight: 1120g
- Cable Length: 1.5M