76342-314LF - DUBOX™ : 28 Position PCB Mounted Receptacle Through Mount, Top Entry, Double Row



ACTIVE

RoHS compatible

www.fci.com

Mating Half

- 77313-101-28LF
- 95278-101-28LF

Specifications

General	
Hold Down Style	No Locating Pegs
Number of contacts (per row)	14
Number of contacts (Total)	28
Number of rows	2
Orientation	Vertical
Packaging	Tube
Mating half	Mates with 0.64 mm (0.025 in.) Square pins.
Series Number	76342
Dimensional	
Thickness (Board)	1.6 mm (0.062 in.) or 2.36 mm (0.093 in.)
Footprint (Board)	2.54 mm x 2.54 mm (0.1 in. x 0.1 in.)
Electrical	
Current rating	3A max. per Contact/2A max. per Contact for Full Load
Resistance (Contact)	15 milli ohms Initial, 20 milli ohms After test
Resistance (Insulation)	100000 M-ohms
Voltage rating	1000V rms
Mechanical	
Insertion force	1.50N (150 gf) per Contact
Withdrawal Force	0.3N (30 gf) min. per Contact
Mounting	
Solder process	Compatible with Wave Soldering Processes
Physical	
Color (Housing)	Blue
Material (Contact)	Phosphor Bronze
Material (Housing)	Glass - Filled Thermoplastic Polyester
Plating (Contact area)	0.76 µm (30 µin.) Gold

Plating (Tail)	3.81µm (150 µin.) Tin-Lead
Underplating (Contact)	1.27 µm (50 µin.) Nickel
Flammability rating	UL 94 V-0
Temperature (Range)	-65 °C to +125 °C

Approvals / Certifications

UL File Number	E66906
CSA File Number	LR46923
Approvals / Certifications	UL and CSA Approved

PRODUCT NUMBER
76342–YXXXLF

- WHEN NEEDED, SUFFIX LETTER "LF" INDICATES THE PRODUCT IS RoHS COMPATIBLE, SEE NOTE 10
- OPTIONAL LETTER
  H: HIGH TEMPERATURE PRODUCT.
  C: PACKAGED IN SHORT TUBE.
- NUMBER OF POSITIONS PER ROW: 02 TO 50.
- PLATING CODE
  3= 0.76µm GOLD ON CONTACT AREA.
  3.81µm TIN–LEAD ON TAIL.
  4= 5µm TIN–LEAD ON CONTACT AREA.
  3.81µm TIN–LEAD ON TAIL.

WHEN SUFFIX "LF" IS REQUIRED, 2µm MIN MATTE TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.





NOTES:

1 – HOUSING MAT'L: THERMOPLASTIC GLASS FILLED FLAME RETARDANT PER UL 94 V–O
LOW TEMPERATURE: COLOR BLUE
HIGH TEMPERATURE: COLOR GREY.

2 – TERMINAL MATERIAL: PHOSPHOR BRONZE.

3 – 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.
5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.

4 – TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: (Nx2.54)–0.08=20.24 mm

5 – RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a – PLATING:
– "LF" MEANS THE PRODUCT IS LEAD–FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.

b – MANUFACTURING PROCESS COMPATIBILITY
– THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c – LABELING:
– MEETS PACKAGING SPECS AS PER GS–14–920

d – LEGAL STATEMENT: SEE GS–22–008

6 – END STAND–OFFS FOR 2x2 UP TO 2X5 POS
NO END STAND–OFFS FOR 2x6 UP TO 2x50 POS

ltr	ecn no	dr	date
S	F10342	DLE	01.06.12
T	F04–0347	DLE	04.09.27
U	F06–0137	DLE	06.02.27
V	F06–0204	DLE	06.06.20
W	F11–0043	JCO	12.02.22
R	F10110	GCO	01.01.16

sheet index	revision	W	B
	sheet	1	2

mat'l. code: SEE NOTES 1 & 2
surface: ISO 1302
tolerance: ISO 406 ISO 1101
tolerances unless otherwise specified: angles ±2°; linear ±0.3
projection
mm
scale 5:1

dr	D LEGRAND	04.09.27
engr	P NIZZI	04.09.27
chr	D LEGRAND	04.09.27
appd	P NZ	04.09.27

product family: DUBOX
title: BtB RECEPT. VERT DR TMT
dwg no: 76342
sheet 1 of 2
size: A3
type: CUSTOMER Drawing

PDM: Rev:W
STATUS:Released
Printed: Mar 20, 2012

Copyright FCI
FCIconnect.com
form: A3



RECOMMENDED HOLE PATTERN

mat'l. code				surface		tolerance		projection	product family
SEE SHEET 1				ISO 1302	√	ISO 406 ISO 1101			DUBOX
ltr	ecn no	dr	date	tolerances unless otherwise specified					title
A	F04–0347	DLE	04.09.27	angles	linear	±0.3		mm	BtB RECEPT. VERT DR TMT
B	F06–0204	DLE	06.06.20						
				±2°				scale 5:1	
				dr	D LEGRAND	04.09.27			dwg no 76342 — sheet 2 of 2 — size A4
				engr	P NIZZI	04.09.27			
				chr	D LE	04.09.27			
				appd	P NZ	04.09.27			type CUSTOMER Drawing
sheet index	revision sheet								

form: A4

FCIconnect.com
Copyright FCI
PDM: Rev:W STATUS:Released Printed: Mar 20, 2012