


## 2/2-way proportional valve




Type 2833 can be combined with...




**Type 8605**

Digital control electronics  
Cable plug version




**Type 8605**

Digital control electronics  
DIN-rail version



**Type 2508**

Cable plug




**Type 8611**

Universal controller

- High sensitivity
- 0 ... 16 bar <sup>1)</sup>
- DN 0.8 ... 4 mm
- 1/8", 1/4" or sub-base
- EEx approvals optional

The direct-acting proportional valve Type 2833 can be used as a control valve for process control and is suitable for technical vacuum. Low hysteresis, high repeatability and high sensitivity ensure superior regulation behaviour. Thanks to an elastomeric sealing, the valve closes tightly and securely.

### Circuit function A



Direct acting 2-way  
proportional valve,  
normally closed

Valve control takes place through the control electronics of Type 8605, which converts an analogue input signal into a PWM signal<sup>2)</sup>.

Further, functional features of the Type 8605 electronic control unit:

- Temperature compensation for coil heating by internal current regulation
- Simple zero and span settings
- Ramp function to dampen fast status changes

<sup>1)</sup> Pressure data [bar]: Overpressure with respect to atmospheric pressure


<sup>2)</sup> PWM pulse-width modulation

<sup>3)</sup> Characteristic data of control behaviour depends on process conditions

| Technical Data - valve                    |   |
|---|---|
| <b>Body material</b>                      | Brass, Stainless steel                                      |
| <b>Seal material</b>                      | FKM, EPDM on request  |
| <b>Media</b>                              | Neutral gases, liquids                                      |
| <b>Medium temperature</b>                 | -10 ... +90 °C  |
| <b>Ambient temperature</b>                | max. +55 °C   |
| <b>Viscosity</b>                          | max. 21 mm <sup>2</sup> /s                                  |
| <b>Operating voltage</b>                  | 24 V DC   |
| <b>Power consumption</b>                  | 9 W   |
| <b>Duty cycle</b>                         | 100 % continuously rated                                    |
| <b>Port connection</b>                    | Sub-base, G 1/8, G 1/4, NPT 1/8, NPT 1/4, others on request |
| <b>Electric connection</b>                | Cable plug Type 2508 acc. to DIN EN 175301-803 Form A       |
| <b>Installation</b>                       | As required, preferably with actuator in upright position   |
| <b>Rotation time (10 - 90%)</b>           | <20ms   |
| <b>Typical control data <sup>3)</sup></b> |   |
| Hysteresis                                | < 5 %   |
| Repeatability                             | < 0.5 % FS.   |
| Sensitivity                               | < 0.25 % FS   |
| Turn-down ratio                           | 1:100   |
| <b>Protection class - valve</b>           | IP65  |

### Technical data - control electronics Type 8605 (see separate datasheet)

Characteristics of a proportional valve



Advice for valve sizing

In continuous flow applications, the choice of appropriate valve size is much more important than with on/off valves. The optimum size should be selected such that the resulting flow in the system is not unnecessarily reduced by the valve. However, a sufficient part of the pressure drop should be taken across the valve even when it is fully opened.

**Recommended value:  $\Delta p_{\text{valve}} > 30\%$  of total pressure drop within the system**

**For that reason take advantage of Bürkert competent engineering services during the planning phase!**

Determination of the kv value

| Pressure drop                          | kv value for liquids [m <sup>3</sup> /h] | kv value for gases [m <sup>3</sup> /h]                     |
|--|--|--|
| Subcritical<br>$p_2 > \frac{p_1}{2}$   | $= Q \sqrt{\frac{\rho}{1000 \Delta p}}$  | $= \frac{Q_N}{514} \sqrt{\frac{T_1 \rho_N}{p_2 \Delta p}}$ |
| Supercritical<br>$p_2 < \frac{p_1}{2}$ | $= Q \sqrt{\frac{\rho}{1000 \Delta p}}$  | $= \frac{Q_N}{257 p_1} \sqrt{T_1 \rho_N}$                  |

- $k_v$  Flow coefficient [m<sup>3</sup>/h]<sup>1)</sup>
- $Q_N$  Standard flow rate [m<sup>3</sup>/h]<sup>2)</sup>
- $p_1$  Inlet pressure [bar]<sup>3)</sup>
- $p_2$  Outlet pressure [bar]<sup>3)</sup>
- $\Delta p$  Differential pressure  $p_1 - p_2$  [bar]
- $\rho$  Density [kg/m<sup>3</sup>]
- $\rho_N$  Standard density [kg/m<sup>3</sup>]
- $T_1$  Temperature if fluid medium [(273+t)K]


<sup>1)</sup> measured for water,  $\Delta p = 1$  bar, via the device

<sup>2)</sup> Standard conditions at 1.013 bar<sup>3)</sup> and 0 °C (273K)

<sup>3)</sup> Absolute pressure

## Ordering chart

### All valves with FKM seal

| Control function  | Orifice [mm] | Port connection | kvs value water [m <sup>3</sup> /h] <sup>1)</sup> | Qn value [l/min] <sup>2)</sup> | Maximum pressure [bar] <sup>3)</sup> | Coil power consumption [W] | Maximum coil current [mA] | Item no. Brass body | Item no. Stainless steel body |
|---|--------------|-----------------|---|--------------------------------|--------------------------------------|----------------------------|---------------------------|---------------------|-------------------------------|
|  | 0.8          | sub-base FB01   | 0.018   | 19                             | 16                                   | 9                          | 400                       | 175 860             | 175 861                       |
|   |              | G 1/8           | 0.018   | 19                             | 16                                   | 9                          | 400                       | 175 862             | 175 863                       |
|   |              | NPT 1/8         | 0.018   | 19                             | 16                                   | 9                          | 400                       | 175 864             | 175 865                       |
|   | 1.2          | sub-base FB01   | 0.040   | 43                             | 12                                   | 9                          | 400                       | 175 866             | 175 867                       |
|   |              | G 1/8           | 0.040   | 43                             | 12                                   | 9                          | 400                       | 175 868             | 175 869                       |
|   |              | NPT 1/8         | 0.040   | 43                             | 12                                   | 9                          | 400                       | 175 870             | 175 871                       |
|   | 1.5          | sub-base FB01   | 0.060   | 65                             | 10                                   | 9                          | 400                       | 175 872             | 175 873                       |
|   |              | G 1/8           | 0.060   | 65                             | 10                                   | 9                          | 400                       | 175 874             | 175 875                       |
|   |              | NPT 1/8         | 0.060   | 65                             | 10                                   | 9                          | 400                       | 175 876             | 175 877                       |
|   | 2.0          | sub-base FB01   | 0.100   | 108                            | 8                                    | 9                          | 400                       | 175 878             | 175 879                       |
|   |              | G 1/8           | 0.100   | 108                            | 8                                    | 9                          | 400                       | 175 880             | 175 891                       |
|   |              | NPT 1/8         | 0.100   | 108                            | 8                                    | 9                          | 400                       | 175 892             | 175 893                       |
|   |              | G 1/4           | 0.100   | 108                            | 8                                    | 9                          | 400                       | 175 896             | 175 900                       |
|   | 2.5          | NPT 1/4         | 0.100   | 108                            | 8                                    | 9                          | 400                       | 175 901             | 175 902                       |
|   |              | sub-base FB01   | 0.150   | 162                            | 5                                    | 9                          | 400                       | 175 922             | 175 923                       |
|   |              | G 1/4           | 0.150   | 162                            | 5                                    | 9                          | 400                       | 175 924             | 175 926                       |
|   | 3.0          | NPT 1/4         | 0.150   | 162                            | 5                                    | 9                          | 400                       | 175 927             | 175 928                       |
|   |              | sub-base FK01   | 0.220   | 237                            | 3.5                                  | 9                          | 400                       | 175 929             | 175 930                       |
|   |              | G 1/4           | 0.220   | 237                            | 3.5                                  | 9                          | 400                       | 175 932             | 175 933                       |
|   | 4.0          | NPT 1/4         | 0.220   | 237                            | 3.5                                  | 9                          | 400                       | 175 938             | 175 939                       |
| sub-base FK01   |              | 0.320           | 345   | 2                              | 9                                    | 400                        | 175 940                   | 175 941             |                               |
| G 1/4   |              | 0.320           | 345   | 2                              | 9                                    | 400                        | 175 942                   | 175 943             |                               |
| NPT 1/4   |              | 0.320           | 345   | 2                              | 9                                    | 400                        | 175 944                   | 175 945             |                               |

<sup>1)</sup> **kVs value:** Flow rate value for water, measured at +20 °C and 1 bar pressure differential over a fully opened valve.

<sup>2)</sup> **Qn value:** Flow rate value for air with inlet pressure of 6 bar(1), 1 bar pressure differential and +20 °C.

<sup>3)</sup> **Pressure data [bar]:** Overpressure with respect to atmospheric pressure

**Please note** that the valves are delivered without control electronics unit and cable plug (see Accessory Ordering Information).

### Further versions on request



#### Materials

Seal material FFKM - Resistant to aggressive media  
Seal material EPDM



#### Analytical

Oxygen version  
Part oil-, fat- and silicon free



#### Electrical connection

12 V Coil



#### Approvals

Ex version - II 2G EEx m IIC T4, PTB No. 02 ATEX 2094X with or without terminal box  
UR  
CSA

## Ordering chart for accessories

### Cable plug Type 2508 according to DIN EN 175301-803 Form A


The delivery of a cable plug includes the flat seal and fixing screw

| Circuitry            | Voltage / frequency | Item no. |
|----------------------|---------------------|----------|
| None                 | 0 - 250 V AC/DC     | 008 376  |
| None, with 3 m cable | 0 - 250 V AC/DC     | 783 573  |

### Electronic Control Type 8605

Please see Datasheet

Dimensions [mm]



For product inquiries, use the specification sheet for proportional valves!

**Note**

You can fill out the fields directly in the PDF file before printing out the form.

**Design data for proportional valves**

▶ Please fill out this form and send to your local Bürkert Sales Centre\* with your inquiry or order

|                 |                |
|-----------------|----------------|
| Company         | Contact person |
| Customer no.    | Dept.          |
| Address         | Tel./Fax       |
| Town / Postcode | E-Mail         |

|   |                                   |  |
|---|-----------------------------------|--|
| <input type="checkbox"/> = Mandatory fields                   | <input type="text"/> Quantity     | <input type="text"/> Desired delivery date                         |
| <b>Process data</b>   |                                   |  |
| <input type="checkbox"/> Medium                               | <input type="text"/>              |  |
| <input type="checkbox"/> State of medium                      | <input type="checkbox"/> liquid   | <input type="checkbox"/> gaseous <input type="checkbox"/> vaporous |
| <input type="checkbox"/> Medium temperature                   | <input type="text"/> °C           |  |
| <input type="checkbox"/> Maximum flow rate                    | $Q_{nom} =$ <input type="text"/>  | Unit: <input type="text"/>   |
| <input type="checkbox"/> Minimum flow rate                    | $Q_{min} =$ <input type="text"/>  | Unit: <input type="text"/>   |
| <input type="checkbox"/> Inlet pressure at nominal operation  | $p_1 =$ <input type="text"/>      | barg   |
| <input type="checkbox"/> Outlet pressure at nominal operation | $p_2 =$ <input type="text"/>      | barg   |
| <input type="checkbox"/> Maximum inlet pressure               | $p_{1max} =$ <input type="text"/> | barg   |
| <input type="checkbox"/> Ambient temperature                  | <input type="text"/> °C           |  |
| <b>Additional specifications</b>                              |                                   |  |
| <input type="checkbox"/> Body material                        | <input type="checkbox"/> Brass    | <input type="checkbox"/> Stainless steel                           |
| <input type="checkbox"/> Seal material                        | <input type="checkbox"/> FKM      | <input type="checkbox"/> other <input type="text"/>                |

**Note** Please state all pressure values as **overpressures with** respect to atmospheric [barg].

To find your nearest Bürkert facility, click on the orange box →

[www.burkert.com](http://www.burkert.com)

In case of special application conditions, please consult for advice.

We reserve the right to make technical changes without notice.

0703/2\_EU-en\_00891978