


## Specification sheet floodlight Goliath 250 +

- **PROFESSIONAL FLOODLIGHT « GOLIATH 250 + »**
  - NEON TUBE COMPACT 55W = 300 WATTS INCANDESCENT LIGHT
  - LONG LIFETIME : 8000 HOURS
  - RUBBER STRAP
  - 2 SOCKETS OUTLETS 16A WITH SHUTTERS
  - NEOPRENE CABLE 5M HO7RNF3G1, 5mm<sup>2</sup>
  - OIL & ACID RESISTANT CABLE
  - LIGHT SWITCH
  - STRONG AND SCATTERED LIGHT – COLD LIGHTING – NON GLARING – SHOCK RESISTANT
  - 4000 LUMEN
  - IP54
  - TELESCOPIC TRIPODE FITTING (HEIGHT: 2,50 m / 360 °)
  - WEIGHT : 3,3 Kg
  - DIMENSIONS : 316 x 316 x 94
  - USE : OUTDOOR / INDOOR USE UNDER ALL WEATHER

Code EAN : 5702128218163



### SCANELEC

Siège :  
1, Village d'Entreprises  
78680 Epône  
Tél : +33 (0)1 41 29 71 70  
Fax : +33 (0)1 30 90 12 42

SAS au Capital de 800.000 €  
RCS Versailles B 348480 674

Siret 348 480 674 000 53  
N°TVA FR 90 348 480 674

APE 4652Z