

## Datasheet

# HSS 5mm Jobber Drill Bit Plain Shank

RS Stock number [213-203](#)



### Description:

HSS TiN Coated, High Speed Steel Titanium nitride coated drill bit.

### Product Details:

- Straight shank
- Right hand cutting
- DIN338; BS328-ISO235/1
- Standard : DIN338 right hand spiral
- Material : HSS M2
- Point Angle : 118°
- Surface : Tin-coated

# Dimension:

| RS Stock No. | Dia.(mm) | Overall Length(mm) | Flute Length(mm) |
|--------------|----------|--------------------|------------------|
| 213-887      | 1.0      | 34                 | 12               |
| 213-900      | 1.1      | 36                 | 14               |
| 213-310      | 1.2      | 38                 | 16               |
| 213-893      | 1.3      | 38                 | 16               |
| 213-376      | 1.4      | 40                 | 18               |
| 213-871      | 1.5      | 40                 | 18               |
| 213-859      | 1.6      | 43                 | 20               |
| 213-433      | 1.7      | 43                 | 20               |
| 213-865      | 1.8      | 46                 | 22               |
| 213-972      | 1.9      | 46                 | 22               |
| 213-916      | 2.0      | 49                 | 24               |
| 213-966      | 2.1      | 49                 | 24               |
| 213-950      | 2.2      | 53                 | 27               |
| 213-944      | 2.3      | 53                 | 27               |
| 213-938      | 2.4      | 57                 | 30               |
| 213-922      | 2.5      | 57                 | 30               |
| 213-843      | 2.6      | 57                 | 30               |
| 213-764      | 2.7      | 61                 | 33               |
| 213-758      | 2.8      | 61                 | 33               |
| 213-427      | 2.9      | 61                 | 33               |
| 213-411      | 3.0      | 61                 | 33               |
| 213-382      | 3.1      | 65                 | 36               |
| 213-405      | 3.2      | 65                 | 36               |
| 213-398      | 3.3      | 65                 | 36               |
| 213-742      | 3.4      | 70                 | 39               |
| 213-304      | 3.5      | 70                 | 39               |
| 213-720      | 3.6      | 70                 | 39               |
| 213-714      | 3.7      | 70                 | 39               |
| 213-736      | 3.8      | 75                 | 43               |
| 213-837      | 3.9      | 75                 | 43               |