

Type BMB-A Series

Key Features

- Effective EMI Protection
- Wide Frequency Characteristics
- High Soldering Heat Resistance
- Various Package Sizes Available
- Suited to a Variety of Applications




The BMB A Series of beads cover a wide range of impedance characteristics. The chip beads have a monolithic organic material construction that minimizes the effect of electromagnetic interference. These are high loss types for general use. This series is offered in 04:02, 06:03 and 08:05 package sizes.

Specifications

Part Number	Impedance (ohms) at 100MHz (±25%)	DC Resistance (ohms) maximum	Rated Current (mA) maximum	
BMB-1E-0030A-N2	30	0.15	500	
BMB-1E-0120A-N2	120	0.25		
BMB-1E-0300A-N2	300	0.45		
BMB-1E-0470A-N2	470	0.55	300	
BMB-1E-0600A-N2	600	0.65	200	
BMB-1J-0030A-N2	30	0.2	400	
BMB-1J-0040A-N2	40			
BMB-1J-0060A-N2	60			
BMB-1J-0080A-N2	80	0.4	300	
BMB-1J-0100A-N2	100		200	
BMB-1J-0120A-N2	120		200	
BMB-1J-0180A-N2	180	0.5		
BMB-1J-0220A-N8A	220	0.5		
BMB-1J-0240A-N2	240			
BMB-1J-0300A-N2	300			
BMB-1J-0450A-N2	450	0.7		150
BMB-1J-0600A-N8	600			
BMB-1J-01000A-N2	1000		1.0	
BMB-2A-0010A-N1	10	0.1	600	
BMB-2A-0017A-N2	17			
BMB-2A-0030A-N1	30			
BMB-2A-0080A-N4	80	0.3	400	
BMB-2A-0120A-N1	120		300	
BMB-2A-0120A-N2				
BMB-2A-0120A-N4				
BMB-2A-0150A-N1	150	0.5	250	
BMB-2A-0220A-N4	220			
BMB-2A-0300A-N1	300			
BMB-2A-0400A-N2	400	0.6	200	
BMB-2A-0600A-N1	600			
BMB-2A-0600A-N2				
BMB-2A-0600A-N4			0.8	100
BMB-2A-1000A-N4	1000			
BMB-2A-1200A-N4	1200			
BMB-2A-1500A-N4	1500	1.0		
BMB-2A-2000A-N4	2000			
BMB-2A-2700A-N4	2700			

Type BMB-A Series


Chip Dimensions



Size	Code	L	W	t	a
0402	1E	1.0 ±0.10	0.5 ±0.10	0.5 ±0.10	0.25 ±0.10
0603	1J	1.6 ±0.15	0.8 ±0.15	0.8 ±0.15	0.3 ±0.20
0805	2A	2.0 ±0.20	1.2 ±0.20	0.9 ±0.20	0.5 ±0.30


Operating Temperature Range: -55°C to +125°C

Characteristic Curves




Type BMB-A Series

Characteristic Curves (continued)



Type BMB-A Series

Characteristic Curves (continued)



TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.

Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this datasheet, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this datasheet are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.